


DOOR NUMBER	QTY	OPENING		ACTUAL		MODEL	JAMB			MOUNTING		LOCK	PANELS WIDE	PANELS HIGH	SECTION NUMBER OPEN FOR GLASS								JOB:	DISTR:	CONTR:	ARCH:	NR:2904948						
		WIDTH	HEIGHT	WIDTH	HEIGHT		W	S	M	ANGLE	BRKT				1	2	3	4	5	6	7	8											



APSEN AP200C - 2" Thick, 26-Gauge Exterior, 27-Gauge Interior




- EXTERIOR COLOR
 - White
 - Brown
 - Almond
 - Sandstone
 - Charcoal
 - Black
 - Desert Tan
 - Bronzestone
 - Medium Oak
 - Walnut
 - PostPaint
- Face Style
 - Colonial
 - Colonial Recessed
 - Ranch
 - Ranch Recessed
 - Mixed
 - Mixed Recessed
 - Flush
 - Plank
- Pattern Name
 - Carriage House
 - MP-1
 - MP-2
 - MP-3
 - MP-4
 - MP-5
 - MP-6
 - MP-7
 - MP-8
 - MP-9
 - MP-10
 - MP-11
 - MP-12
 - MP-13
 - MP-14
 - MP-15
 - MP-16
 - MP-17

- Window style (Plastic Inserts)
- Colonial
- Ranch
- Cascade Colonial
- Stockton colonial
- Sherwood Colonial
- Sunburst Colonial
- Waterton colonial
- Prairie colonial
- Cascade Ranch
- Stockton ranch
- Sunburts ranch (2 Window)
- Sunburst Ranch (4 Window)
- Waterton ranch
- Stockbridge Ranch
- Arched Stockbridge Ranch
- Arched Stockton Ranch (2 Window)

Interior Locking - spring loaded slide bolt engages slot in track, operable from inside only - may be mounted either side

Locking - omitted.

Locks should not be supplied with an electric operated door without a lock interlock switch.



DOOR NUMBER	QTY	OPENING		ACTUAL		MODEL	JAMB			MOUNTING	LOCK	PANELS WIDE	PANELS HIGH	SECTION NUMBER OPEN FOR GLASS								JOB: DISTR: CONTR: ARCH:		
		WIDTH	HEIGHT	WIDTH	HEIGHT		W	S	M					ANGLE	BRKT	1	2	3	4	5	6		7	8




NR: 2904948

TABLE #1
PANEL CHART

Number of Panel	Door Width +/- 1/16"		End Sill Width +/- 1/8"	Mult Spacing +/- 1/16"	Dim "A" +/- 1/8"
2	4	3/8	2.75	3.00	42.875
	5	11 3/16	14.156		42.875
3	5	11 5/16	2.75	3.00	65.813
	7	10 1/8	14.156		65.813
4	7	10 1/4	2.75	3.00	88.75
	8	1 1/8	4.1875		88.75
4	8	1 1/4	2.75	4.00	91.75
	9	10 1/16	13.156		91.75
5	9	10 3/16	2.75	3.25	112.69
	11	8	13.656		112.69
6	11	8 1/8	2.75	3.00	134.63
	13	6 15/16	14.156		134.63
7	13	7 1/16	2.75	3.00	157.56
	14	5 7/16	7.9375		157.56
7	14	5 9/16	2.75	4.75	168.06
	15	5 7/8	8.9063		168.06
8	15	6	2.75	3.00	180.5
	16	9 5/8	10.563		180.5
8	16	9 3/4	2.75	5.25	196.25
	18	4 13/16	12.281		196.25
9	18	4 15/16	2.75	4.50	215.44
	19	3 3/4	8.1563		215.44
10	19	3 7/8	2.75	3.00	226.38
	21	2 11/16	14.156		226.38
11	21	1 3/4	2.75	3.00	249.31
	23	1 5/8	14.156		249.31
12	23	1 3/4	2.75	3.00	272.25
	24	2	8.875		272.25

TABLE #2
Panel Layout CHART



Residential Doors							
	Door Model	Section Width	U-bar 20 Ga. (.82#/ft) (Qty/Door)	U-bar 18 Ga. (1.15#/ft) (Qty/Door)	Section No.	Special Notes	
Aspen	AP200C (4 sections)	11'-9" thru 16'-2"	(1)		4		
		16'-3" thru 18'-3"		(3)	1, 3, & 4		
		18'-4" thru 20'-2"		(4)	1, 2, 3, & 4		
	AP200C (5 sections)	11'-9" thru 14'-8"	(1)			5	
		14'-9" thru 16'-2"	(3)			1, 3, & 5	
		16'-3" thru 18'-2"			(3)	1, 3, & 5	
		18'-3" thru 20'-2"			(5)	1, 2, 3, 4, & 5	
	AP200C (6 sections)	11'-9" thru 14'-8"	(1)			6	
		14'-9" thru 16'-2"	(3)			1, 3, & 6	
		16'-3" thru 18'-2"			(3)	1, 3, & 6	
		18'-3" thru 20'-2"			(6)	1, 2, 3, 4, 5 & 6	