



DOOR NUMBER	QTY	OPENING		ACTUAL		MODEL	JAMB			MOUNTING		LOCK	PANELS WIDE	PANELS HIGH	SECTION NUMBER OPEN FOR GLASS								JOB:		
		WIDTH	HEIGHT	WIDTH	HEIGHT		W	S	M	ANGLE	BRKT				1	2	3	4	5	6	7	8			
																							DISTR:		
																							CONTR:		
																								ARCH:	NR:2904949

APSEN AP138C – 1 3/8" Thick, 26-Gauge Exterior, 27-Gauge Interior

- Skin Material (See Note Above)
- Polyurethane Insulation (R-Value AP138C = 13.08) Interior skin removed for Clarity
- TRUSSING
- None
 - Ubar (18 or 20 Gauge)



EXTERIOR COLOR

- White
- Brown
- Almond
- Sandstone
- Charcoal
- Black
- Desert Tan
- Bronzitone
- Medium Oak
- Walnut
- PostPaint

Face Style

- Colonial
- Colonial Recessed
- Ranch
- Ranch Recessed
- Mixed
- Mixed Recessed
- Flush
- Plank

Pattern Name

- Carriage House
- MP-1 MP-9
- MP-2 MP-10
- MP-3 MP-11
- MP-4 MP-12
- MP-5 MP-13
- MP-6 MP-14
- MP-7 MP-15
- MP-8 MP-16
- MP-17


Window style (Plastic Inserts)

- | | |
|--|---|
| <input type="checkbox"/> Colonial | <input type="checkbox"/> Stockton ranch |
| <input type="checkbox"/> Ranch | <input type="checkbox"/> Sunburts ranch (2 Window) |
| <input type="checkbox"/> Cascade Colonial | <input type="checkbox"/> Sunburst Ranch (4 Window) |
| <input type="checkbox"/> Stockton colonial | <input type="checkbox"/> Waterton ranch |
| <input type="checkbox"/> Sherwood Colonial | <input type="checkbox"/> Stockbridge Ranch |
| <input type="checkbox"/> Sunburst Colonial | <input type="checkbox"/> Arched Stockbridge Ranch |
| <input type="checkbox"/> Waterton colonial | <input type="checkbox"/> Arched Stockton Ranch (2 Window) |
| <input type="checkbox"/> Prarie colonial | |
| <input type="checkbox"/> Cascade Ranch | |

Interior Locking – spring loaded slide bolt engages slot in track. operable from inside only – may be mounted either side

Locking – omitted.

Locks should not be supplied with an electric operated door without a lock interlock switch.



Door Designs

- Flush
- Colonial
- Ranch
- Carriage House


DOOR NUMBER	QTY	OPENING		ACTUAL		MODEL	JAMB		MOUNTING	LOCK	PANELS WIDE	PANELS HIGH	SECTION NUMBER OPEN FOR GLASS								JOB:		
		WIDTH	HEIGHT	WIDTH	HEIGHT		W	S	M				ANGLE	BRKT	1	2	3	4	5	6		7	8
																					DISTR:		
																					CONTR:		
																					ARCH:		
																			NR:2904949				



TABLE #1
PANEL CHART

Number of Panel	Door Width +/- 1/16"		End Stile Width +/- 1/8"	Mutt Spacing +/- 1/16"	Dim "A" +/- 1/8"
2	4	3/8	2.75	3.00	
	5	11 3/16	14.156		42.875
3	5	11 5/16	2.75	3.00	65.813
	7	10 1/8	14.156		65.813
4	7	10 1/4	2.75	3.00	88.75
	8	1 1/8	4.1875		88.75
4	8	1 1/4	2.75	4.00	91.75
	9	10 1/16	13.156		91.75
5	9	10 3/16	2.75	3.25	112.69
	11	8	13.656		112.69
6	11	8 1/8	2.75	3.00	134.63
	13	6 15/16	14.156		134.63
7	13	7 1/16	2.75	3.00	157.56
	14	5 7/16	7.9375		157.56
7	14	5 9/16	2.75	4.75	168.06
	15	5 7/8	8.9063		168.06
8	15	6	2.75	3.00	180.5
	16	9 5/8	10.563		180.5
8	16	9 3/4	2.75	5.25	196.25
	18	4 13/16	12.281		196.25
9	18	4 15/16	2.75	4.50	215.44
	19	3 3/4	8.1563		215.44
10	19	3 7/8	2.75	3.00	226.38
	20	2	7.8125		226.38

TABLE #2
Panel Layout CHART



Residential Doors						
	Door Model	Section Width	U-bar 20 Ga. (.82#/ft)	U-bar 18 Ga. (1.15#/ft)	Section No.	Special Notes
			(Qty/Door)	(Qty/Door)		
Aspen	AP138C (4 sections)	11'-9" thru 16'-2"	(1)		4	
		16'-3" thru 18'-3"		(3)	1, 3, & 4	
		18'-4" thru 20'-2"		(4)	1, 2, 3, & 4	
	AP138C (5 sections)	11'-9" thru 14'-8"	(1)		5	
		14'-9" thru 16'-2"	(3)		1, 3, & 5	
		16'-3" thru 18'-2"		(3)	1, 3, & 5	
		18'-3" thru 20'-2"		(5)	1, 2, 3, 4, & 5	
	AP138C (6 sections)	11'-9" thru 14'-8"	(1)		6	
		14'-9" thru 16'-2"	(3)		1, 3, & 6	
		16'-3" thru 18'-2"		(3)	1, 3, & 6	
		18'-3" thru 20'-2"		(6)	1, 2, 3, 4, 5 & 6	