



TECHNICAL DRAWING SPECIFICATION				UNLESS OTHERWISE SPECIFIED:			TITLE:		
				DIMENSIONS ARE IN MILIMETER [INCHES] Sanding Area : --- Control Specs: Blue Wording			RESP1231212 (FPH9015)		
				APPROVED BY: GM / CUSTOMER			SIZE: A		
				COMMENTS:			DWG. NO. PSS022		
							REV 1		
Max. Area (Sanded)	Min Area (Sanded)	Max. Weight (Sanded)	Min. Weight (Sanded)				SCALE: 1:1		
1106 mm2	1000 mm2	1.69 kg/m	1.50 kg/m				MATERIAL : RESYSTA		
							SHEET 1 OF 1		