


21 [0,827]
20 [0,787]



Min. 3,8 [0.1496]

Min. 3,5 [0.1378]

201 [7,913]
199 [7,835]

3 [0,1181]

TECHNICAL SPECIFICATION				UNLESS OTHERWISE SPECIFIED:			NAME		DATE		TITLE					
				DIMENSIONS ARE IN MILIMETER [INCHES] Sanding Area : --- Control Specs : Blue Wording			DRAWN BY		WL LIM		6.5.2016		RESP340812 (FPH20020)			
							APPROVED BY									
							COMMENTS :				SIZE		DWG. NO.		REV	
											A		PSS048A		0	
Max. Area (Sanded)		Min. Area (Sanded)		Max. Weight (Sanded)		Min. Weight (Sanded)		SCALE: 1:1		MATERIAL : RESYSTA			SHEET 1 OF 1			
2086 mm2		1862 mm2		3.13 kg/m		2.79 kg/m										