



TECHNICAL DRAWING SPECIFICATION				UNLESS OTHERWISE SPECIFIED:			TITLE:										
				DIMENSIONS ARE IN MILIMETER [INCHES]			<b>CP95</b>										
				Drill Hole Interval : 8" +/-0.25" Sanding Area : <span style="color: red;">---</span> <span style="color: blue;">---</span> <span style="color: red;">---</span> Control Specs : <span style="color: blue;">Blue Wording</span>													
<table border="1"> <tr> <td>Max. Area (Sanded)</td> <td>Min Area (Sanded)</td> <td>Max. Weight (Sanded)</td> <td>Min. Weight (Sanded)</td> </tr> <tr> <td>760 mm2</td> <td>722 mm2</td> <td>1.18 kg/m</td> <td>1.11 kg/m</td> </tr> </table>				Max. Area (Sanded)	Min Area (Sanded)	Max. Weight (Sanded)	Min. Weight (Sanded)	760 mm2	722 mm2	1.18 kg/m	1.11 kg/m	DRAWN BY: WL LIM    DATE: 1.10.15 APPROVED BY: GM / CUSTOMER COMMENTS:			SIZE: <b>A</b> DWG. NO.: <b>PSS047</b>		REV: <b>1</b>
Max. Area (Sanded)	Min Area (Sanded)	Max. Weight (Sanded)	Min. Weight (Sanded)														
760 mm2	722 mm2	1.18 kg/m	1.11 kg/m														
				SCALE: 1:1			MATERIAL : RESYSTA		SHEET 1 OF 1								