



REVISION HISTORY				
REV.	DATE	NOTE	EON	BY
A	1/22/2015	RELEASE	6963	SHC
B	4/16/2015	ADD CLEARANCE NOTES	6963	SHC

APPROVED YES NO AS MARKED

APPROVED BY: _____

DATE: _____

SPECIFICATIONS

- SPEED:** UP TO 52" (1321 mm) / SEC WITH STANDARD VARIABLE FREQUENCY DRIVE. TOP SPEED IS DEPENDENT ON DOOR SIZE.
- SIZE:** MAXIMUM: 24' (7315 mm) WIDE x 24' (7315 mm) HIGH
MINIMUM: 8' (2438 mm) WIDE x 8' (2438 mm) HIGH
- CURTAIN MATERIAL:** 100 MIL POLYPROPYLENE
 BLUE GREEN GRAY ORANGE RED WHITE
- SIDE FRAMES:** BLACK POWDER COATED ALUMINUM EXTRUSION.
- DRIVE SYSTEM:** 2 HP. (1.5 kW) MOTOR, VARIABLE FREQUENCY DRIVE, TRAXION DRIVE SYSTEM - CONSISTING OF A DRIVE GEAR, DRIVE SPHERES AND A COMPOSITE EDGE MATERIAL WHICH IS HEAT WELDED TO THE CURTAIN. COUNTER WEIGHTED CURTAIN ROLL-UP TUBE.
- ELECTRICAL REQUIREMENTS:** SINGLE PHASE: 220V - 240V, 60 HZ
 208V, 60 HZ
THREE PHASE: 230V, 60 HZ
 480V, 50/60 HZ
 460V, 60 HZ
 575V, 60 HZ
- VISION OPTIONS:** NONE
 20" x 20" (508 mm x 508 mm) REPLACIBLE VISION PANELS
 20" x 20" (508 mm x 508 mm) GRAY SCREEN WITH REMOVABLE CLEAR COVER
- CONTROL BOX:** I-COMM DIGITAL CONTROLLER, VARIABLE FREQUENCY DRIVE. MAIN ENCLOSURE NEMA 4X - 14" (356 mm) x 16" (406 mm) x 8" (203 mm) STANDARD COMPACT USER INTERFACE.
- CURTAIN RETENTION:** WEAR RESISTANT LEXAN WIND GUIDES KEEP TENSION ON THE CURTAIN THE ENTIRE LENGTH OF THE SIDE FRAME. INCLUDES TRUE AUTO RE-FEED SYSTEM IN CASE OF ACCIDENTAL IMPACTS TO CURTAIN.
- WINDBAR OPTIONS:** FRONT WINDBAR (OPTIONAL)
- SAFETY FEATURES:** SOFT EDGE TECHNOLOGY, THRU-BEAM PHOTO EYE MOUNTED AT 18" (457 mm) AND 54" (1372 mm). COUNTER WEIGHT BELT MONITORING SYSTEM.
- OPTIONAL EQUIPMENT:** NON-POWERED MANUAL OPENING
 HIGH WIND LOCK PLATES (16' NON-BREAKAWAY SECTION)
- WARRANTY:** LIMITED 1-YEAR PARTS AND LABOR ON ALL COMPONENTS, INCLUDING ELECTRICAL. EXCLUSIVE 1-YEAR MONEY BACK GUARANTEE OF CUSTOMER SATISFACTION.

USE THIS DRAWING FOR DOORS WITHOUT A REAR WINDBAR THAT HAVE A SLOPED SHROUD
SEE DRAWING 7832A001 FOR DOORS WITHOUT A REAR WINDBAR THAT HAVE NO SHROUD OR A FLAT SHROUD
FOR DOORS WITH A REAR WINDBAR SEE DRAWINGS 7832A003 & 7832A004

OMITTING DRIVE AND COUNTERWEIGHT SHROUDS DOES NOT REDUCE SIDE CLEARANCE REQUIREMENTS

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		TOLERANCES	
X	+ 0.00	SIZE	DATE
XX	+ 0.00	BY	DATE
XXX	+ 0.00	CHKD	DATE
ANGLE	+ 0.05	APP'D	DATE

DESIGN	DATE	SCALE	PART	SHEET	OF
7832A002	10/3/2014	1:20	-	1	1

RITE-HITE DOORS INC.

FASTRAX XL ARCHITECTURAL APPROVAL
STANDARD PROJECTION
SLOPED SHROUD

REV	DATE	BY	DESCRIPTION
A	1/22/2015	SHC	RELEASE
B	4/16/2015	SHC	ADD CLEARANCE NOTES