




SECTIONAL VIEW - GEARLESS TYPE 1R



PLAN VIEW - GEARLESS TYPE 1R




2 MOUNTING POSITIONS CENTER OR SIDE




FINAL RAIL BRACKET RB1	BELOW THE MOTOR CONSULT YOUR REPRESENTATIVE FOR EXACT LOCATION
INTERMEDIATE RAIL BRACKET RB2	32\"/>
BOTTOM RAIL BRACKET RB3	44\"/>

HALL BUTTON NEEDED AT ALL FLOORS




CLEAR INSIDE CAB WIDTH	CLEAR INSIDE CAB LENGTH	A FINISHED RUNWAY WIDTH		B FINISHED RUNWAY LENGTH		C RAIL CENTER LINE		D DOOR CENTER LINE			
		mm	Inches	mm	Inches	mm	Inches	mm	Inches		
914	36	1219	48	1346	53	1397	55	787	31	781	30 3/4
914	36	1372	54	1346	53	1549	61	838	33	781	30 3/4
914	36	1524	60	1346	53	1702	67	914	36	781	30 3/4
1016	40	1372	54	1448	57	1549	61	838	33	883	34 3/4

FORCES



ENTRANCE SIDE LEGEND



RESIDENTIAL ELEVATOR GEARLESS TYPE 1R

CUSTOMER: \_\_\_\_\_ DATE: \_\_\_\_\_  
 PROJECT: \_\_\_\_\_ PROJECT LINE: \_\_\_\_\_  
 LOCATION: \_\_\_\_\_ CONTROLLED BY: \_\_\_\_\_  
 THE INFORMATION DISCLOSED HEREIN IS THE EXCLUSIVE PROPERTY OF Savaria  
 AND MAY NOT BE USED BY OTHERS WITHOUT WRITTEN CONSENT.  
 SHEET 1/1