





SECTIONAL VIEW - GEARLESS TYPE 1L



PLAN VIEW - GEARLESS TYPE 1L






2 MOUNTING POSITIONS CENTER OR SIDE



BELOW THE MOTOR CONSULT YOUR CONCORD REPRESENTATIVE FOR EXACT RBS LOCATION	32" (813mm) INTERVALS AFTER 2nd BOTTOM BRACKET
4" (102mm) & 7" (180mm) ABOVE PIT FLOOR	

CLEAR INSIDE CAB WIDTH		CLEAR INSIDE CAB LENGTH		A FINISHED RUNWAY WIDTH		B FINISHED RUNWAY LENGTH		C RAIL CENTER LINE		D DOOR CENTER LINE	
mm	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Inches
914	36	1219	48	1346	53	1397	55	787	31	781	30 3/4
914	36	1372	54	1346	53	1549	61	838	33	781	30 3/4
914	36	1524	60	1346	53	1702	67	914	36	781	30 3/4
1016	40	1372	54	1448	57	1549	61	838	33	883	34 3/4



RESIDENTIAL ELEVATOR
GEARLESS TYPE 1L

CUSTOMER: _____ DATE: _____
 PROJECT: _____ DRAWING NO.: _____
 LOCATION: _____ COMPANY BY: _____

savaria

1/1