



CLASSIFICATION

TELECAB CAPACITY	800 LBS (327 KG)
COLOR (METALLIC FINISH)	WHITE
PLATEGLASS INT	SMOKE
CAB DOOR OPERATION	MANUAL
	HYDRAULIC DOOR CLOSER
	POWER OPERATED
POWER	110 VAC + 12 VDC DOWN STD
	120 VDC UP + DOWN
	120 VAC/20 Hz
HALL STATION	TRIPSOLE MOUNTED
	FLUSH MOUNTED
SEATING WALL	WOOD
	CONCRETE
LEVEL SERVED	2 LEVELS
NUMBER OF OPENINGS	1 OPENING
MAX. WINDING SPEED	2000 FPM
RELIEF PRESSURE	SPRINGLESS MAN
DRIVE SYSTEM	1 TO 2 CHAIN HYDRAULIC
CHAINS	8/16, QTY: 2
CONTROLLER	RELAY LOGIC
OPERATION	CONSTANT PRESSURE, ANTI-CREEP FEATURE
FLOOR PLUG	PROVIDED

SAFETY FEATURES

- 1) CAB COTTERED BRUSH LOCK
- 2) UNDER PANEL SAFETY SENSOR
- 3) EMERGENCY STOP AND ALARM
- 4) EMERGENCY BATTERY LEADINGS
- 5) EMERGENCY LEADINGS
- 6) FULLY ENCLOSED DRIVE TOWER
- 7) PRESSURE RELIEF VALVE TO PREVENT PLATFORM OVERLOAD
- 8) BLACK CHAIR SAFETY SEAT
- 9) SELFPHONE IN CAB
- 10) MALFUNCTION LIGHT IN CAB
- 11) REDUNDANT PRESSURE SWITCH

CODE

THIS LIFT IS DESIGNED, MANUFACTURED AND INSTALLED IN ACCORDANCE WITH THE FOLLOWING STANDARDS:

- ANSI A17.1 PART 7 2007-08, CSA B44 2007-08, IEC AND IECI
- DESIGNER'S RESPONSIBILITY IS LIMITED TO THE DESIGN AND MANUFACTURING REQUIREMENTS OF THESE CODES AND EXCLUDES REQUIREMENTS RELATIVE TO THE INSTALLATION AND MAINTENANCE.

CUSTOMER:

PROJECT:

DATE:

PROJECTION: **TOLERANCES IF NOT SPECIFIED:** FRACTIONS: ±1/8" (3)

SCALE:

DRAWN BY:

DATE:

DRAWING #: **REV#:** **PAGE:** **TITLE:**

