



ELEVATION VIEW TYPE-2

# V1504

TOP VIEW TYPE-2



TYPICAL ENCLOSURE

TYPICAL ENCLOSURE WITH EXTENSION & CLEAR PLEXIGLASS DOME & VENTILATION SYSTEM & DOOR OPERATOR

FORCES





TABLE 1- MAST HEIGHT\*

Max. Travel mm (Inches)	Extension Height mm (Inches)					Mast Height Approx with Gate with 4.188" CAP	
	2388 (94")	1778 (70")	1168 (46")	559 (22")	254 (10")	mm	Inches
1219 (48")	1				1	2748	108.188
1524 (60")	1			1		3053	120.188
1829 (72")	1		1			3662	144.188
2438 (96")	1	1				4272	168.188
2743 (108")	1	1				4272	168.188
3048 (120")	2					4882	192.188
3658 (144")	2			1		5440	214.188
4267 (168")	2		1			6050	238.188
4877 (192")	2	1				6660	262.188
5486 (216")	3					7269	286.188
6096 (240")	3			1		7828	308.188
6706 (264")	3		1			8438	332.188
7010 (276")	3		1		1	8692	342.188

\*EXAMPLE TABLE WITH 3" PIT, DIMENSIONS VARY WITH TRAVEL

TABLE 2 - ENCLOSURE DIMENSION

CLEAR INSIDE CAB WIDTH		CLEAR INSIDE CAB LENGTH		A FINISHED RUNWAY WIDTH		B FINISHED RUNWAY LENGTH		C TOWER CENTER LINE		D DOOR CENTER LINE (IN CASE OF 36" DOOR)	
mm	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Inches
914	36	1219	48	1437	56 9/16	1376	54 3/16	687	27 1/16	794	31 1/4
914	36	1372	54	1437	56 9/16	1529	60 3/16	764	30 1/16	794	31 1/4
914	36	1524	60	1437	56 9/16	1681	66 3/16	840	33 1/16	794	31 1/4
1067	42	1219	48	1589	62 9/16	1376	54 3/16	687	27 1/16	870	34 1/4
1067	42	1372	54	1589	62 9/16	1529	60 3/16	764	30 1/16	870	34 1/4
1067	42	1524	60	1589	62 9/16	1681	66 3/16	840	33 1/16	870	34 1/4



THE INFORMATION DISCLOSED HEREIN IS THE EXCLUSIVE PROPERTY OF



AND MAY NOT BE USED BY OTHERS WITHOUT PRIOR WRITTEN CONSENT

TITLE:  
V1504  
TYPE - 2

CUSTOMER	DATE:	08/24/2009	REVISION:	002
	SCALE:	1:1	DATE:	03/23/2012
PROJECT:	DRAFTER:	PHILLIP TRAN	SHEET 1 OF 1	
LOCATION:	DRAWING NO.:	V1504 PLUS ENCLOSURE		