

# V1504 TOP VIEW TYPE-1L





TABLE 1- MAST HEIGHT\*

Max. Travel mm (Inches)	Extension Height mm (Inches)				Mast Height with 4.188" CAP	
	2388 (94")	1778 (70")	1168 (46")	559 (22")	254 (10")	
1219 (48")	1				1	2748 108.188
1524 (60")	1			1		3053 120.188
1829 (72")	1		1			3662 144.188
2438 (96")	1	1				4272 168.188
2743 (108")	1	1				4272 168.188
3048 (120")	2					4882 192.188
3658 (144")	2			1		5440 214.188
4267 (168")	2		1			6050 238.188
4877 (192")	2	1				6660 262.188
5486 (216")	3					7269 286.188
6096 (240")	3			1		7828 308.188
6706 (264")	3		1			8438 332.188
7010 (276")	3		1		1	8692 342.188

\*EXAMPLE TABLE WITH 3" PIT, DIMENSIONS VARY WITH TRAVEL

## ANCHOR POINTS



## FORCES







TABLE 2- HOISTWAY DIMENSION

CLEAR INSIDE CAB WIDTH		CLEAR INSIDE CAB LENGTH		A FINISHED RUNWAY WIDTH		B FINISHED RUNWAY LENGTH		C TOWER CENTER LINE		D DOOR CENTER LINE (IN CASE OF 36" DOOR)	
mm	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Inches	mm	Inches
914	36	1219	48	1359	53 1/2	1354	53 5/16	624	24 9/16	781	30 3/4
914	36	1372	54	1359	53 1/2	1507	59 5/16	700	27 9/16	781	30 3/4
914	36	1524	60	1359	53 1/2	1659	65 5/16	776	30 9/16	781	30 3/4
1067	42	1219	48	1511	59 1/2	1354	53 5/16	624	24 9/16	857	33 3/4
1067	42	1372	54	1511	59 1/2	1507	59 5/16	700	27 9/16	857	33 3/4
1067	42	1524	60	1511	59 1/2	1659	65 5/16	776	30 9/16	857	33 3/4



THE INFORMATION DISCLOSED HEREIN IS THE EXCLUSIVE PROPERTY OF

**savaria™**

AND MAY NOT BE USED BY OTHERS WITHOUT PRIOR WRITTEN CONSENT

TITLE: V1504 TYPE - 1L

CUSTOMER: \_\_\_\_\_

PROJECT: \_\_\_\_\_

LOCATION: \_\_\_\_\_

DATE: 08/24/2009

SCALE: 1:1

DRAFTER: VINID C

DRAWING NO: V1504 PLUS HOISTWAY

REVISION: 001

06/25/2010

SHEET 1 OF 1