

ELEVATION VIEW TYPE-4 45 OPEN




TABLE 1- MAST HEIGHT*


Max. Travel mm (Inches)	Extension Height mm (Inches)					Mast Height with 4.188" CAP	
	2388 (94")	1778 (70")	1168 (46")	559 (22")	254 (10")	mm	Inches
1219 (48")	1				1	2748	108.188
1524 (60")	1			1		3053	120.188
1829 (72")	1		1			3662	144.188
2438 (96")	1	1				4272	168.188
2743 (108")	1	1				4272	168.188
3048 (120")	2					4882	192.188
3658 (144")	2			1		5440	214.188
4267 (168")	2		1			6050	238.188
4877 (192")	2	1				6660	262.188
5486 (216")	3					7269	286.188
6096 (240")	3			1		7828	308.188
6706 (264")	3		1			8438	332.188
7010 (276")	3		1		1	8692	342.188

*EXAMPLE TABLE WITH 3" PIT, DIMENSIONS VARY WITH TRAVEL

V1504

TOP VIEW TYPE-4 45 OPEN

ANCHOR POINTS



FORCES







TABLE 2- HOISTWAY DIMENSION

CLEAR INSIDE CAB WIDTH	CLEAR INSIDE CAB LENGTH	A FINISHED RUNWAY WIDTH		B FINISHED RUNWAY LENGTH		C TOWER CENTER LINE		D DOOR CENTER LINE (IN CASE OF 36" DOOR)	
		mm	Inches	mm	Inches	mm	Inches	mm	Inches
914	36	1219	48	1359	53 1/2	1354	53 5/16	624	24 9/16
914	36	1372	54	1359	53 1/2	1507	59 5/16	700	27 9/16
914	36	1524	60	1359	53 1/2	1659	65 5/16	776	30 9/16
1067	42	1219	48	1511	59 1/2	1354	53 5/16	624	24 9/16
1067	42	1372	54	1511	59 1/2	1507	59 5/16	700	27 9/16
1067	42	1524	60	1511	59 1/2	1659	65 5/16	776	30 9/16



THE INFORMATION DISCLOSED HEREIN IS THE EXCLUSIVE PROPERTY OF

AND NOT BE USED BY OTHERS WITHOUT PRIOR WRITTEN CONSENT

TITLE: V1504 TYPE -4 45 OPEN

CUSTOMER: PROJECT: LOCATION:

DATE: 06/25/2010 REVISION: 000 06/25/2010 SHEET 1 OF 1

SCALE: 1:1 DRAFTER: VINOD C DRAWING NO: V1504 PLUS HOISTWAY