


CLASSIFICATION: S/MR LIFT
MODEL: K2
CAPACITY: 350Lbs [155kg] for less than 45 deg angle staircase
SPEED: 0.075 m/sec [15"/min]
POWER SUPPLY: 110V, 6A, 60Hz, SINGLE PHASE
MOTOR: 1/3 HP-24 VDC / 110V AC CHARGER
DRIVE SYSTEM: RACK AND PINION
CONTROLLER:
MODEL: LUT125
TYPE: CPFS
ETLP: 102118528MTL-001
CONTROL VOLTS: 24VDC
MFR.: LUTRON

SPECIFICATIONS:
ANGLE OF STAIRCASE: 31° TO 45°
LENGTH OF STAIRWAY: MAX 265'
LOCATION: INDOOR
SEAT COVERING: VINYL
COLOR: WHITE
CALL STATION: A REMOTE FOR RESIDENTIAL
SAFETY FEATURE: OVERSPEED GOVERNOR

WOODEN THREAD:
 ANCHOR EACH BRACKET SET USING A MINIMUM OF 4X Ø1/4 X 2" WOOD SCREW
REINFORCED CONCRETE:
 ANCHOR EACH BRACKET SET USING A MINIMUM OF 4X SLEEVE ANCHORS 1/4-2"
METAL PLATE / BLOCK:
 ANCHOR EACH BRACKET SET USING A MINIMUM OF 4X TRHU BOLT 1/4"
BRACKET POSITION:
 WITHIN 18 INCHES [457] OF EACH END OF EACH SECTION OF TRACK IN THE CENTER OF EVERY SECTION OF TRACK LONGER THAN 4 FEET

OPTIONS




SIDE OF INSTALLATION: LEFT RIGHT
QTY OF RAIL SECTION: _____ (94" EACH)
PADDLE ON ARM: YES
BLU-LINE: YES
FLIP-UP RAIL: YES
BRACKET EXTENSION: YES



SURFACE HALL CALL FOR PUBLIC APPLICATION ONLY


	W (SEAT WIDTH)	K (SEAT DEPTH)	H (SEAT HEIGHT)
SEAT AT NORMAL WIDTH	17.24" (438mm)	17.94" (455mm)	24.02" (610.6 mm)
SEAT AT MIDDLE WIDTH	19.8" (503mm)	17.40" (442mm)	25.00" (635mm)
SEAT AT BIGGEST WIDTH	20.50" (520mm)	18.50" (470mm)	27.11" (689mm)

SUPPORT LOAD DIAGRAM



	A (WALL FRONT TO WALL)	B (WALL BACK TO THE WALL)	C (WALL TO FRONT OF SEAT REELS)
SEAT AT NORMAL WIDTH	8"	34"	2 4/8"
SEAT AT MIDDLE WIDTH	8 3/4"	1 1/4"	3 3/8"
SEAT AT BIGGEST WIDTH	9 3/4"	2 1/4"	4 1/2"

(31°-55°) (RAIL ANGLE)	D (SEAT TO FOOTPRESS)	E (SEAT HEIGHT)	F (FOOTREST HEIGHT)
31°	16.70"	21.60"	4.90"
35°	16.94"	21.61"	4.881"
40°	17.125"	22.08"	4.90"
45°	17.24"	21.93"	4.68"
50°	17.32"	22.125"	4.81"
55°	17.32"	22.24"	4.91"



LH SHOWN

CUSTOMER:	DATE:	Part No. K2
PROJECT:	REVISION DATE:	Variant No. N/A
ADDRESS:	COMPLETED BY: ALMIX B	SAVARIA
	JOB No.:	SHEET No. 1 OF 1