

M200 MAX LENGTH (IN) MAX WEIGHT (LB) 75 55

THESE DRAWINGS SHOW OUR INTERPRETATION OF THE PRINCIPAL PLANS AND SPECIFICATIONS. THEY ARE SUBMITTED AS CHECK PRINTS REQUIRING REVIEW AND POSSIBLE REVISIONS TO DETAILS AND/OR DIMENSIONS BEFORE FABRICATION OF MATERIALS CAN BEGIN, DRAWING PACKAGE MUST MATCH O.P.M. ORDER AND BE RETURNED SIGNED AND DATED. IF THERE ARE SIZE DISCREPANCIES BETWEEN THIS DRAWING PACKAGE AND O.P.M. ORDER, THESE DRAWING SUPERCEDE O.P.M. DIMENSIONS. IF CONSIDERABLY DIFFERENT, A RE-SUBMITTAL OF O.P.M. ORDER WILL BE REQUIRED. THIS SIGNATURE INDICATES PURCHASER'S FULL ACCEPTANCE OF DETAILS SHOWN AND THE PRODUCT IN CONFORMANCE TO SAME. THESE DESIGNS AND DRAWINGS ARE THE EXCLUSIVE PROPERTY OF SMOKE GUARD, INC. AND ARE NOT TO BE USED OR DUPLICATED WITHOUT PERMISSIONS. DRAWN: TLM



287 N. Maple Grove Boise, ID 83704 800.574.0330 www.smokeguard.com

- M200/400 GENERAL NOTES:

  1. CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.
- 2. TOLERANCE: FLOOR TO CEILING VARIANCE MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE..
- ORDER LENGTHS TO BE AT 1/4" INCREMENTS ONLY.
- DIMENSIONS DO NOT INCLUDE HEADS OF
- EXTERNAL FASTENERS.


  5. SMOKE RATING FOR ENCLOSURE ABOVE HOUSING DESIGNED BY OTHERS.
- INTERNAL MOTORS ARE ACCESSIBLE
- THROUGH HOUSING OPENING WHEN UNIT IS

REVISION REVISION DESCRIPTION D1 9.16.20 INITIAL RELEASE

ONFIGURATION: ----ROJECT: ----

ESIGN SET: D1 B ODEL: M200 200 DETAILS

9.16.20





287 N. Maple Grove Boise, ID 83704 800.574.0330

### www.smokeguard.com

- M200/400 GENERAL NOTES:
  1. CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.
- 2. TOLERANCE: FLOOR TO CEILING VARIANCE MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE..
- 3. ORDER LENGTHS TO BE AT 1/4" INCREMENTS ONLY.
- 4. DIMENSIONS DO NOT INCLUDE HEADS OF EXTERNAL FASTENERS.

  5. SMOKE RATING FOR ENCLOSURE ABOVE HOUSING DESIGNED BY OTHERS.


  6. INTERNAL MOTORS ARE ACCESSIBLE
- THROUGH HOUSING OPENING WHEN UNIT IS

REVISION				
REVISION NUMBER	REVISION DATE	REVISION DESCRIPTION		
D1	9.16.20	INITIAL RELEASE		

	DESIGN SET: D1	SIZE
	MODEL: M200	В
NS.	SHEET TITLE: M200 ELEVATION DETAILS	SHEET

DRAWN: TLM 9.16,2020

THESE DRAWINGS SHOW OUR INTERPRETATION OF THE PRINCIPAL PLANS AND SPECIFICATIONS. THEY ARE SUBMITTED AS CHECK PRINTS REQUIRING REVIEW AND POSSIBLE REVISIONS TO DETAILS AND/OR DIMENSIONS. BEFORE FABRICATION OF MATERIALS CAN BEGIN, DRAWING PACKAGE MUST MATCH O.P.M. ORDER AND BE RETURNED SIGNED AND DATED. IF THERE ARE SIZE DISCREPANCIES BETWEEN THIS DRAWING PACKAGE AND O.P.M. ORDER, THESE DRAWING SUPERCEDE O.P.M. DIMENSIONS. IF CONSIDERABLY DIFFERENT, A RE-SUBMITTAL OF O.P.M. ORDER WILL BE REQUIRED. THIS SIGNATURE INDICATES PURCHASER'S FULL ACCEPTANCE OF DETAILS SHOWN AND THE PRODUCT IN CONFORMANCE TO SAME. THESE DESIGNS AND DRAWINGS ARE THE EXCLUSIVE PROPERTY OF SMOKE GUARD, INC. AND ARE NOT TO BE USED OR DUPLICATED WITHOUT PERMISSIONS.



M200 READY STATE DETAILS
SCALE: 1/2" = 1'-0"

SMOKE GUARD<sup>®</sup>

287 N. Maple Grove Boise, ID 83704 800.574.0330

# www.smokeguard.com

- M200/400 GENERAL NOTES:
  1. CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.
- 2. TOLERANCE: FLOOR TO CEILING VARIANCE MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE..
- 3. ORDER LENGTHS TO BE AT 1/4" INCREMENTS ONLY.
- 4. DIMENSIONS DO NOT INCLUDE HEADS OF
- EXTERNAL FASTENERS.

  5. SMOKE RATING FOR ENCLOSURE ABOVE HOUSING DESIGNED BY OTHERS.
- 6. INTERNAL MOTORS ARE ACCESSIBLE THROUGH HOUSING OPENING WHEN UNIT IS

REVISION				
REVISION NUMBER	REVISION DATE	REVISION DESCRIPTION		
D1	9.16.20	INITIAL RELEASE		


ONFIGURATION: ----PROJECT: ----DIST.: ----

DESIGN SET: D1 ODEL: M200

200 READY STATE DETAILS

B DRAWN: TLM 9.16.2

THESE DRAWINGS SHOW OUR INTERPRETATION OF THE PRINCIPAL PLANS AND SPECIFICATIONS. THEY ARE SUBMITTED AS CHECK PRINTS REQUIRING REVIEW AND POSSIBLE REVISIONS TO DETAILS AND/OR DIMENSIONS. BEFORE FABRICATION OF MATERIALS CAN BEGIN, DRAWING PACKAGE MUST MATCH O.P.M. ORDER AND BE RETURNED SIGNED AND DATED. IF THERE ARE SIZE DISCREPANCIES BETWEEN THIS DRAWING PACKAGE AND O.P.M. ORDER, THESE DRAWING SUPERCEDE O.P.M. DIMENSIONS. IF CONSIDERABLY DIFFERENT, A RE-SUBMITTAL OF O.P.M. ORDER WILL BE REQUIRED. THIS SIGNATURE INDICATES PURCHASER'S FULL ACCEPTANCE OF DETAILS SHOWN AND THE PRODUCT IN CONFORMANCE TO SAME. THESE DESIGNS AND DRAWINGS ARE THE EXCLUSIVE PROPERTY OF SMOKE GUARD, INC. AND ARE NOT TO BE USED OR DUPLICATED WITHOUT PERMISSIONS.





THESE DRAWINGS SHOW OUR INTERPRETATION OF THE PRINCIPAL PLANS AND SPECIFICATIONS. THEY ARE SUBMITTED AS CHECK PRINTS REQUIRING REVIEW AND POSSIBLE REVISIONS TO DETAILS AND/OR DIMENSIONS BEFORE FABRICATION OF MATERIALS CAN BEGIN, DRAWING PACKAGE MUST MATCH O.P.M. ORDER AND BE RETURNED SIGNED AND DATED. IF THERE ARE SIZE DISCREPANCIES BETWEEN THIS DRAWING PACKAGE MUST MATCH O.P.M. ORDER, THESE DRAWING SUPERCEDE O.P.M. DIMENSIONS. IF CONSIDERABLY DIFFERENT, A RE-SUBMITTAL OF O.P.M. ORDER WILL BE REQUIRED. THIS SIGNATURE INDICATES PURCHASER'S FULL ACCEPTANCE OF DETAILS SHOWN AND THE PRODUCT IN CONFORMANCE TO SAME. THESE DESIGNS AND DRAWINGS ARE THE EXCLUSIVE PROPERTY OF SMOKE GUARD, INC. AND ARE NOT TO BE USED OR DUPLICATED WITHOUT PERMISSIONS.



287 N. Maple Grove Boise, ID 83704 800.574.0330 www.smokeguard.com

- M200/400 GENERAL NOTES:
  1. CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.
- 2. TOLERANCE: FLOOR TO CEILING VARIANCE MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE..
- 3. ORDER LENGTHS TO BE AT 1/4" INCREMENTS ONLY.
- 4. DIMENSIONS DO NOT INCLUDE HEADS OF
- EXTERNAL FASTENERS.

  5. SMOKE RATING FOR ENCLOSURE ABOVE HOUSING DESIGNED BY OTHERS.
- 6. INTERNAL MOTORS ARE ACCESSIBLE THROUGH HOUSING OPENING WHEN UNIT IS

REVISION				
REVISION NUMBER	REVISION DATE	REVISION DESCRIPTION		
D1	9.16.20	INITIAL RELEASE		


ONFIGURATION: ----PROJECT: ----DIST.: ----

ESIGN SET: D1 B ODEL: M200

200 DEPLOYED DETAILS DRAWN: TLM 9.16.202

FILE LOCATION::\\OXIDE2\company\Sales\_Integration\CAD\Web Design Details\M200\_400





120 VAC BY OTHERS GREEN--GROUND WHITE--NEUTRAL BLACK--HOT

LOW VOLTAGE CONNECTIONS -FROM SMOKE DETECTOR

120 VAC POWER (60 HZ, 2A MAX): FOR MOTOR REWIND/RETRACTION OF SCREEN AFTER DEPLOYMENT. BY OTHERS: -PROVIDE CONDUIT AND WIRE -(AFTER UNIT IS INSTALLED) REMOVE TEMPORARY PLUG AND WIRE 120 VAC TO HIGH VOLTAGE WIRES IN THE JUNCTION BOX ON THE SIDE OF THE HOUSING -PROVIDE GROUND HOUSING

JUNCTION BOX

HOUSING JUNCTION BOX (ACCESS THROUGH INSIDE OF HOUSING)

-BY OTHERS

120VAC

HOUSING: SIDE VIEW

AUXILIARY CONTACT.

THIS DRAWING ILLUSTRATES THAT UP TO

TO THE SAME END-OF-DIODE AT AN

INITIATING DEVICE (SMOKE DETECTOR)

4 HOUSINGS CAN BE WIRED, IN PARALLEL,

120VAC

INITIATING DEVICE 120VAC BY OTHERS INITIATING **DEVICE** 120VAC END OF LINE DIODE ALARM CIRCUIT

ALL WIRING BY OTHERS

SMOKE DETECTOR (UL 268 COMPLIANT) BY OTHERS: -PROVIDE A NORMALLY CLOSED AUXILIARY CONTACT THAT IS ACTIVATED WHEN THE SMOKE DETECTOR GOES INTO ALARM. THIS CONTACT DOES NOT ACTIVATE ON GENERAL BUILDING ALARM. NO VOLTAGE EXISTS ACROSS THE CONTACT -(WHEN THERE ARE MULTIPLE-UNIT SYSTEM IN A COMMON AREA THAT ARE ACTIVATED BY A SINGLE SMOKE DETECTOR); WIRE UP TO 4 SMOKE GUARD UNITS TO A SINGLE SMOKE DETECTOR,

IN PARALLEL. MULTIPLE UNITS ON A COMMON FLOOR THAT ARE ACTIVATED BY THE SAME SMOKE DETECTOR REQUIRE ALARM CIRCUIT WIRING FROM THE DETECTOR TO EACH UNIT. THE PRINTED CIRCUIT BOARD IN EACH HOUSING MUST SEE THE END-OF-LINE DIODE ON THE SMOKE DETECTOR.

END-OF-LINE DIODE: BY OTHERS: -INSTALL 3.9V OR 2 WATT END-OF-LINE DIODE (FURNISHED BY SMOKE GUARD) AT INITIATING DEVICE. -IN SERIES WITH THE NORMALLY CLOSED AUXILIARY CONTACT.

ALARM CIRCUIT: (24 VDC ,40 MA IN MONITORING MODE; NO VOLTAGE OR AMPS IN ALARM MODE) BY OTHERS:

-PROVIDE AN ALARM CIRCUIT FROM THE NORMALLY CLOSED AUXILIARY CONTACT OF THE SMOKE DETECTOR TO THE LOW VOLTAGE WIRES IN THE JUNCTION BOX ON THE SIDE OF THE HOUSING, USING STRANDED WIRES, IN RACEWAYS OR CONDUIT.

-(AFTER UNIT IS INSTALLED) TERMINATE THE SMOKE DETECTOR WIRES TO LOW VOLTAGE WIRES IN THE JUNCTION BOX ON THE SIDE OF THE HOUSING.

M200 ELECTRICAL DETAILS SCALE: 1/2" = 1'-0"

GUARD' SMOKE

> 287 N. Maple Grove Boise, ID 83704 800.574.0330 www.smokeguard.com

M200/400 GENERAL NOTES:

CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.

2. TOLERANCE: FLOOR TO CEILING VARIANCE MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE..

ORDER LENGTHS TO BE AT 1/4" INCREMENTS ONLY.

. DIMENSIONS DO NOT INCLUDE HEADS OF EXTERNAL FASTENERS.

SMOKE RATING FOR ENCLOSURE ABOVE HOUSING DESIGNED BY OTHERS

INTERNAL MOTORS ARE ACCESSIBLE THROUGH HOUSING OPENING WHEN UNIT IS

# REVISION REVISION DESCRIPTION DATE D1 9.16.2 INITIAL RELEASE

NFIGURATION: ---ROJECT: ----

DRAWN:

ESIGN SET: D1 B ODFI: M200 00 ELECTRICAL DETAIL

TLM 9.16.2

5 OF 5

THESE DRAWINGS SHOW OUR INTERPRETATION OF THE PRINCIPAL PLANS AND SPECIFICATIONS. THEY ARE SUBMITTED AS CHECK PRINTS REQUIRING REVIEW AND POSSIBLE REVISIONS TO DETAILS AND/OR DIMENSIONS BEFORE FABRICATION OF MATERIALS CAN BEGIN, DRAWING PACKAGE MUST MATCH O.P.M. ORDER AND BE RETURNED SIGNED AND DATED. IF THERE ARE SIZE DISCREPANCIES BETWEEN THIS DRAWING PACKAGE MUD O.P.M. ORDER THESE DRAWING SUPERCEDE O.P.M. DIMENSIONS, IF CONSIDERABLY DIFFERENT, A RE-SUBMITTAL OF O.P.M. ORDER WILL BE REQUIRED. THIS SIGNATURE INDICATES PURCHASER'S FULL ACCEPTANCE OF DETAILS SHOWN AND THE PRODUCT IN CONFORMANCE TO SAME. THESE DESIGNS AND DRAWINGS ARE THE EXCLUSIVE PROPERTY OF SMOKE GUARD, INC. AND ARE NOT TO BE USED OR DUPLICATED WITHOUT