



287 N. Maple Grove Boise, ID 83704 800.574.0330 www.smokeguard.com

M3000 FIRE NOTES:

- 1. SMOKE GUARD FIRE RATED UNITS (HOUSINGS & SIDE GUIDES) TO BE MOUNTED TO A FINISHED, FIRE RATED ASSEMBLY OR STRUCTURE PER YOUR APPLICATION.
- 2. CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.
- TOLERANCE: FLOOR TO CEILING VARIANCE
 MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE.

 4. ORDER LENGTHS TO BE AT 1/4"
- INCREMENTS ONLY.

 5. DIMENSIONS TO NOT INCLUDE HEADS OF EXTERNAL FASTENERS.

 6. STATIC LOADS
- 6.1. HEADBOX: 40 LBS/FT.

- 6.1. HEAUBUX: 40 LBS/FI.
 6.2. FOOTBOX: 40 LBS/FT.
 6.3. GUIDES: 15 LBS/FT.
 7. CONTROLLER CONDUIT BY OTHERS
 8. CONTROLLER CABLE PROVIDED
 9. PROVIDE ACCESS TO CONTROLLER


REVISION		
EVISION IUMBER	REVISION DATE	REVISION DESCRIPTION
D1	7.28.20	INITIAL RELEASE

CONFIGURATION: PROJECT: ----DIST.: ----

DESIGN SET: D1 10DFI: M3000

M3000 ELEVATION, PLAN, & ECTION DETAILS DRAWN: TLM

B





287 N. Maple Grove Boise, ID 83704 800.574.0330 www.smokeguard.com

M3000 FIRE NOTES:

- 1. SMOKE GUARD FIRE RATED UNITS (HOUSINGS & SIDE GUIDES) TO BE MOUNTED TO A FINISHED, FIRE RATED ASSEMBLY OR STRUCTURE PER YOUR APPLICATION.
- 2. CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.
- TOLERANCE: FLOOR TO CEILING VARIANCE MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE.
- 4. ORDER LENGTHS TO BE AT 1/4"
- INCREMENTS ONLY.


 5. DIMENSIONS TO NOT INCLUDE HEADS OF EXTERNAL FASTENERS. 6. STATIC LOADS
- 6.1. HEADBOX: 40 LBS/FT.
- 6.2. FOOTBOX: 40 LBS/FT.
- 6.3. GUIDES: 15 LBS/FT.
- 7. CONTROLLER CONDUIT BY OTHERS
- 8. CONTROLLER CABLE PROVIDED
- 9. PROVIDE ACCESS TO CONTROLLER


REVISION		
REVISION NUMBER	REVISION DATE	REVISION DESCRIPTION
D1	7.28.20	INITIAL RELEASE

ONFIGURATION: PROJECT: ----


ESIGN	SET: D1		SIZE
ODEL:	M3000		B
HEET TITLE 3000 TYP			SHEET
DRAWN:	TLM	7.28.2020	2 OF 5

FILE LOCATION::\\OXIDE2\company\Sales_Integration\CAD\Web Design Details\M3000






M3000-STRUCTURAL MOUNTING
SCALE: 3/4" = 1'-0"




M3000-DROP RATER NOTCH

HEADER @SIDE GUIDE

SCALE: 3/4" = 1'-0"




M3000-SYSTEM AS TESTED-4 HEAD & FOOTBOX SIM. SCALE: 3/4" = 1'-0"



M3000-DROP RATED HEADER

5 POCKET-2 @SIDE GUIDE

SCALE: 3/4" = 1'-0"



M3000-DROP RATED HEADER

6 POCKET-1 @ SIDE GUIDE

SCALE: 3/4" = 1'-0"



287 N. Maple Grove Boise, ID 83704 800.574.0330 www.smokeguard.com

M3000 FIRE NOTES:

- SMOKE GUARD FIRE RATED UNITS (HOUSINGS & SIDE GUIDES) TO BE MOUNTED TO A FINISHED, FIRE RATED ASSEMBLY OR STRUCTURE PER YOUR APPLICATION.
- CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.
- 3. TOLERANCE: FLOOR TO CEILING VARIANCE MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE.
- 4. ORDER LENGTHS TO BE AT 1/4"
- INCREMENTS ONLY.
 5. DIMENSIONS TO NOT INCLUDE HEADS OF EXTERNAL FASTENERS.
- 6. STATIC LOADS 6.1. HEADBOX: 40 LBS/FT.
- 6.2. FOOTBOX: 40 LBS/FT.
- 6.3. GUIDES: 15 LBS/FT.
- 7. CONTROLLER CONDUIT BY OTHERS
- 8. CONTROLLER CABLE PROVIDED
- 9. PROVIDE ACCESS TO CONTROLLER

REVISION		
REVISION NUMBER	REVISION DATE	REVISION DESCRIPTION
D1	7.28.20	INITIAL RELEASE


QUOTE: ---CONFIGURATION: PROJECT: ----

DESIGN SET: D1

MODEL: M3000
SHEET TITLE:
M3000-1 SIDE GUIDES

DRAWN: TLM 7.28.2020 3 0 F S


ER SIZE: 11 X 17




M3000-DROP RATED


HEADER @ HEADBOX

SCALE: 3/4" = 1'-0"




















M3000-DROP RATED NOTCH 6 HEADER @ HEADBOX SCALE: 3/4" = 1'-0"



287 N. Maple Grove Boise, ID 83704 800.574.0330 www.smokeauard.com

M3000 FIRE NOTES:

- 1. SMOKE GUARD FIRE RATED UNITS (HOUSINGS & SIDE GUIDES) TO BE MOUNTED TO A FINISHED FIRE RATED ASSEMBLY OR STRUCTURE PER YOUR APPLICATION.
- 2. CLIENT TO PROVIDE CONTINUOUS MOUNTING SURFACE FOR STRUCTURAL AND SHEET METAL ATTACHMENT.
- TOLERANCE: FLOOR TO CEILING VARIANCE MUST BE WITHIN +/- 1/2" ACROSS LENGTH OF MACHINE.
- 4. ORDER LENGTHS TO BE AT 1/4"
- INCREMENTS ONLY.

 5. DIMENSIONS TO NOT INCLUDE HEADS OF EXTERNAL FASTENERS. 6. STATIC LOADS
- 6.1. HEADBOX: 40 LBS/FT.
- 6.2. FOOTBOX: 40 LBS/FT.
- 6.3. GUIDES: 15 LBS/FT. 7. CONTROLLER CONDUIT BY OTHERS
- 8. CONTROLLER CABLE PROVIDED
- 9. PROVIDE ACCESS TO CONTROLLER


REVISION			
ISION MBER	REVISION DATE	REVISION DESCRIPTION	
01	7.28.20	INITIAL RELEASE	

QUOTE:
CONFIGURATION:
PROJECT:
DIST.:

SIGN SET: D1	SIZE
DDEL: M3000	В
EET TITLE: 000- HEADBOX & FOOTBOX	SHEE

DRAWN: TLM 7.28.2020

FILE LOCATION::\\OXIDE2\company\Sales_Integration\CAD\Web Design Details\M3000





287 N. Maple Grove Boise, ID 83704 800.574.0330 www.smokeguard.com

M3000 ELECTRICAL NOTES: 1. CONTROLLER CONDUIT BY OTHERS

2. CONTROLLER CABLE PROVIDED 3. MAX 30 CONDUIT FEET FROM MAIN

CONTROLLER TO HOUSING

4. INTERNAL MOTORS ARE ACCESSIBLE
THROUGH HOUSING OPENING WHEN UNIT IS

DEPLOYED.

REVISION REVISION DESCRIPTION UMBER DATE INITIAL RELEASE D1 7.28.20

B

QUOTE: ---CONFIGURATION: PROJECT: ----DIST.: ----

DESIGN SET: D1 MODEL: M3000

W3000 ELECTRICAL DETAILS DRAWN: TLM 7.28.202