


UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.

TOLERANCES:	
DECIMAL	ANGULAR
.X ±.03	±.25°
.XX ±.01	
.XXX ±.005	


SURFACE ROUGHNESS $\sqrt{125}$
 REMOVE ALL BURRS AND
 BREAK SHARP EDGES .03 MAX
 SURFACE TEXTURE IN ACCORDANCE
 WITH LATEST ANSI B46.1
 DIMS. & TOL. IN ACCORDANCE
 WITH LATEST ANSI Y14.5

MATERIAL	Alu01
FINISH	

DATE	11/25/2015
CHECKED	
QA	
MFG	
APPROVED	

		6201 27th STREET SACRAMENTO, CA 95822 Phone: (916) 395-4700 (800) 289-4700 Fax: (916) 395-9204	
TITLE			
PDOME 4040 W51.250 L51.250 SGZ			
SIZE	DWG NO	REV	
B	PDOME 4040	1	

PROPRIETARY AND CONFIDENTIAL
 THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
 PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
 A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
 INC., IS PROHIBITED.



SCALE	SHEET 1 OF 2	
-------	--------------	--