

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES


TOLERANCES:	DECIMAL	ANGULAR
.X	±.03	±.25°
.XX	±.01	
.XXX	±.005	

SURFACE ROUGHNESS 125 ✓  
REMOVE ALL BURRS AND  
BREAK SHARP EDGES .03 MAX  
SURFACE TEXTURE IN ACCORDANCE  
WITH LATEST ANSI B46.1  
DIMS. & TOL. IN ACCORDANCE  
WITH LATEST ANSI Y14.5

MATERIAL

FINISH

DATE	11/25/2015
CHECKED	
QA	
MFG	
APPROVED	

		6201 27th STREET SACRAMENTO, CA 95822 Phone: (916) 395-4700 (800) 289-4700 Fax: (916) 395-9204	
TITLE			
PDOME 4080 W52.250 L100.250 SGZ			
SIZE	DWG NO	REV	
B	PDOME 4080	1	
SCALE	SHEET 1 OF 2		

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS  
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,  
INC., IS PROHIBITED.

