

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.


DECIMAL	ANGULAR
.XX ±.03	±.25°
.XXX ±.01	
.XXX ±.005	

125 ✓
SURFACE ROUGHNESS
REMOVE ALL BURRS AND
BREAK SHARP EDGES .03 MAX
SURFACE TEXTURE IN ACCORDANCE
WITH LATEST ANSI B46.1
DIMS. & TOL. IN ACCORDANCE
WITH LATEST ANSI Y14.5


MATERIAL

FINISH

DATE	11/25/2015
CHECKED	
QA	
MFG	
APPROVED	

 SUNOPTICS High Performance Prismatic Daylighting	6201 27th STREET SACRAMENTO, CA 95822 Phone: (916) 395-4700 (800) 289-4700 Fax: (916) 395-9204	
	TITLE PDOME 5050 W63.250 L63.250 SGZ	
SIZE	DWG NO	REV
B	PDOME 5050	1

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
INC., IS PROHIBITED.



SCALE		SHEET 1 OF 2
-------	--	--------------