

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.


TOLERANCES:
DECIMAL ANGULAR
XX ±.03 ±.25°
XXX ±.01
XXXX ±.005

125 ✓
SURFACE ROUGHNESS
REMOVE ALL BURRS AND
BREAK SHARP EDGES .03 MAX
SURFACE TEXTURE IN ACCORDANCE
WITH LATEST ANSI B46.1
DIMS. & TOL. IN ACCORDANCE
WITH LATEST ANSI Y14.5

MATERIAL

FINISH


DATE	11/25/2015
CHECKED	
QA	
MFG	
APPROVED	

 **SUNOPTICS**
High Performance Prismatic Daylighting

6201 27th STREET
SACRAMENTO, CA 95822
Phone: (916) 395-4700
(800) 289-4700
Fax: (916) 395-9204

TITLE
PDOME 5060 W63.625 L75.625 SGZ

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
INC., IS PROHIBITED.



SIZE	B	DWG NO	PDOME 5060	REV	1
------	---	--------	------------	-----	---

SCALE

SHEET 2 OF 2