

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES


TOLERANCES:	DECIMAL	ANGULAR
.X	±.03	±.25°
.XX	±.01	
.XXX	±.005	

SURFACE ROUGHNESS 125 ✓
REMOVE ALL BURRS AND
BREAK SHARP EDGES .03 MAX
SURFACE TEXTURE IN ACCORDANCE
WITH LATEST ANSI B46.1
DIMS. & TOL. IN ACCORDANCE
WITH LATEST ANSI Y14.5

MATERIAL

FINISH

DATE	11/25/2015
CHECKED	
QA	
MFG	
APPROVED	

 <p>High Performance Prismatic Daylighting</p>		6201 27th STREET SACRAMENTO, CA 95822 Phone: (916) 395-4700 (800) 289-4700 Fax: (916) 395-9204	
TITLE			
PDOME 5060 W63.625 L75.625 SGZ			
SIZE		DWG NO	REV
B		PDOME 5060	1
SCALE		SHEET 1 OF 2	

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
INC., IS PROHIBITED.

