

4


3

2

1

B

B



ID FRAME: W51.250" X L51.250"

A

A

A

A

UNLESS OTHERWISE SPECIFIED  
DIMENSIONS ARE IN INCHES.

TOLERANCES:  
DECIMAL      ANGULAR  
XX      ±.03      ±.25°  
.XX      ±.01  
.XXX      ±.005

SURFACE ROUGHNESS      125 ✓  
REMOVE ALL BURRS AND  
BREAK SHARP EDGES .03 MAX  
SURFACE TEXTURE IN ACCORDANCE  
WITH LATEST ANSI B46.1  
DIMS. & TOL. IN ACCORDANCE  
WITH LATEST ANSI Y14.5

MATERIAL

DATE

11/6/2015



**SUNOPTICS**  
High Performance Prismatic Daylighting

6201 27th STREET  
SACRAMENTO, CA 95822  
Phone: (916) 395-4700  
(800) 289-4700  
Fax: (916) 395-9204

CHECKED

QA

FINISH

MFG

APPROVED

TITLE

SIG 4040 W51.250 L51.250 DGZ 900LU MW

SIZE

B

DWG NO

REV

SCALE

SHEET 2 OF 2

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE  
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS  
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,  
INC., IS PROHIBITED.

THIRD ANGLE PROJECTION



4

3

2

1

A