



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.

TOLERANCES:
DECIMAL ANGULAR
XX ±.03 ±.25°
XX ±.01
XXX ±.005

125 ✓
SURFACE ROUGHNESS
REMOVE ALL BURRS AND
BREAK SHARP EDGES .03 MAX
SURFACE TEXTURE IN ACCORDANCE
WITH LATEST ANSI B46.1
DIMS. & TOL. IN ACCORDANCE
WITH LATEST ANSI Y14.5

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
INC., IS PROHIBITED.

MATERIAL

FINISH

THIRD ANGLE PROJECTION

DATE	11/6/2015
CHECKED	
QA	
MFG	
APPROVED	

		6201 27th STREET SACRAMENTO, CA 95822 Phone: (916) 395-4700 (800) 289-4700 Fax: (916) 395-9204	
TITLE			
SIG 4070 W51.250 L87.250 DGZ 900LU MW			
SIZE	DWG NO	REV	
B			
SCALE	SHEET 1 OF 2		