

4


3

2

1

B

B



ID FRAME: W52.250" X L100.250"

A

A

A

A

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.

TOLERANCES:
DECIMAL ANGULAR
XX ±.03 ±.25°
XXX ±.01
XXXX ±.005

SURFACE ROUGHNESS 125 ✓
REMOVE ALL BURRS AND
BREAK SHARP EDGES .03 MAX
SURFACE TEXTURE IN ACCORDANCE
WITH LATEST ANSI B46.1
DIMS. & TOL. IN ACCORDANCE
WITH LATEST ANSI Y14.5

MATERIAL

DRG 01

11/6/2015



SUNOPTICS
High Performance Prismatic Daylighting

6201 27th STREET
SACRAMENTO, CA 95822
Phone: (916) 395-4700
(800) 289-4700
Fax: (916) 395-9204

CHECKED

QA

FINISH

MFG

APPROVED

TITLE

SIG 4080 W52.250 L100.250 DGZ 900LU MW

SIZE

B

DWG NO

REV

SCALE

SHEET 2 OF 2

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
INC., IS PROHIBITED.

THIRD ANGLE PROJECTION



4

3

2

1

A