

4


3

2

1

B

B



ID FRAME: W63.250" X L63.250"

A

A

A

A

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.

TOLERANCES:

DECIMAL	ANGULAR
.X ±.03	±.25°
.XX ±.01	
.XXX ±.005	

SURFACE ROUGHNESS 125 ✓
REMOVE ALL BURRS AND
BREAK SHARP EDGES .03 MAX
SURFACE TEXTURE IN ACCORDANCE
WITH LATEST ANSI B46.1
DIMS. & TOL. IN ACCORDANCE
WITH LATEST ANSI Y14.5

MATERIAL

FINISH

DATE

CHECKED

QA

MFG

APPROVED

11/6/2015



SUNOPTICS
High Performance Prismatic Daylighting

6201 27th STREET
SACRAMENTO, CA 95822
Phone: (916) 395-4700
(800) 289-4700
Fax: (916) 395-9204

TITLE

SIG 5050 W63.250 L63.250 DGZ 900LU MW

SIZE

B

DWG NO


REV

SCALE

SHEET 2 OF 2

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
INC., IS PROHIBITED.

THIRD ANGLE PROJECTION



4

3

2

1

A