

4


3

2

1

B

B



ID FRAME: W63.625" X L75.625"

A

A


A

A


UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES

TOLERANCES:
DECIMAL ANGULAR
XX ±.03 ±.25°
XXX ±.01
XXXX ±.005

SURFACE ROUGHNESS 125 ✓
REMOVE ALL BURRS AND
BREAK SHARP EDGES .03 MAX
SURFACE TEXTURE IN ACCORDANCE
WITH LATEST ANSI B46.1
DIMS. & TOL. IN ACCORDANCE
WITH LATEST ANSI Y14.5

MATERIAL	DRG NO	11/6/2015	 High Performance Prismatic Daylighting		6201 27th STREET SACRAMENTO, CA 95822 Phone: (916) 395-4700 (800) 289-4700 Fax: (916) 395-9204
FINISH	CHECKED		TITLE		
	QA		SIG 5060 W63.625 L75.625 DGZ 900LU MW		
	MFG		SIZE	DWG NO	REV
	APPROVED		B		
			SCALE		SHEET 2 OF 2

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
INC., IS PROHIBITED.



4

3

2

1

A