

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES.

TOLERANCES:	DECIMAL	ANGULAR
.X	±.03	±.25°
.XX	±.01	
.XXX	±.005	

125 ✓
SURFACE ROUGHNESS
REMOVE ALL BURRS AND
BREAK SHARP EDGES .03 MAX
SURFACE TEXTURE IN ACCORDANCE
WITH LATEST ANSI B46.1
DIMS. & TOL. IN ACCORDANCE
WITH LATEST ANSI Y14.5

MATERIAL

FINISH

DATE 11/6/2015

CHECKED

QA

MFG

APPROVED


 **SUNOPTICS**
High Performance Prismatic Daylighting

6201 27th STREET
SACRAMENTO, CA 95822
Phone: (916) 395-4700
(800) 289-4700
Fax: (916) 395-9204

TITLE

SIG 5060 W63.625 L75.625 DGZ 900LU MW

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE
PROPERTY OF SUNOPTICS INC. ANY REPRODUCTION IN PART OR AS
A WHOLE, WITHOUT THE WRITTEN PERMISSION OF SUNOPTICS,
INC., IS PROHIBITED.



SIZE	DWG NO	REV
B		
SCALE	SHEET 1 OF 2	