

****				
ITN	R	V	A	<b>Y</b> ®
Al		A MC		

## IMOTION® TN 110 IN-FLOOR SWING DOOR OPERATOR FLUSH MOUNT BOX

SINGLE DOOR LH CENTER PIVOT APPLICATION

JOB NAME:	DATE:	
DOOR LOCATION:	DOOR NO:	_SHEETOF






TOP VIEW <u>OPTION B</u>


- EXTENDED SHAFT
- SPECIAL REMOVABLE COVER BOX FOR FLOOR COVERING INSTALLATION
- MAX. FLOOR COVERING = 1/2"

PIT DIMENSION 19 3/4"L x 17 3/4"W x 6 7/8"D

FLOOR BOX - OPTION B

Max. Floor covering thickness in







END SECTION B-B

Concrete or Finished Floor

- Weep Drain Required
- (1) Possible Electrical Feed





REFER TO THRESHOLD DETAIL DRAWING FOR DISTANCE FROM BOTTOM OF DOOR SHOE TO FINISHED FLOOR

## NOTES:

- 1. DETAILS NOT TO SCALE.
- 2. ELECTRICAL REQUIREMENTS:
  - 120VAC, 15AMP MIN. TO EACH CONTROLLER LOCATED REMOTE FROM OPERATOR. LOW VOLTAGE CONDUIT RUN FROM EACH CONTROLLER TO OPERATOR BY ELECTRICAL CONTRACTOR.
- 3. DOORS, FRAMES AND HARDWARE BY OTHERS.

PLAN

- 4. 32" CLEAR DOOR OPENING REQUIRED TO MEET A.D.A. REQUIREMENTS.
- 5. DOORS MUST BE NON-LATCHED FOR PROPER OPERATION.
- 6. OPERATOR CAN BE CONFIGURED TO MEET ANSI STANDARDS A156.10 & ANSI A156.19