



## IMOTION® TN 110 IN-FLOOR SWING DOOR OPERATOR FLUSH MOUNT BOX

AUTOMATIC SINGLE DOOR RH INSWING CENTER PIVOT W/ BREAKAWAY APPLICATION

 JOB NAME:
 \_\_\_\_\_\_\_DATE:

 DOOR LOCATION:
 \_\_\_\_\_\_\_DOOR NO:





OPERATOR AND FLOOR BOX
TOP VIEW


## OPTION B


- EXTENDED SHAFT
- SPECIAL REMOVABLE COVER BOX FOR FLOOR COVERING INSTALLATION
- MAX. FLOOR COVERING = 1/2"


  <u>PIT DIMENSION</u>

19 3/4"L x 17 3/4"W x 6 7/8"D

FLOOR BOX - OPTION B









FRONT SECTION

END SECTION B-B





Weep Drain Required

Possible Electrical Feed

Concrete or Finished Floor

REFER TO THRESHOLD DETAIL
DRAWING FOR DISTANCE FROM
BOTTOM OF DOOR SHOE TO

FINISHED FLOOR

## NOTES:

1. DETAILS NOT TO SCALE.

2. ELECTRICAL REQUIREMENTS: 120VAC, 15AMP MIN. TO EACH CONTR

120VAC, 15AMP MIN. TO EACH CONTROLLER LOCATED REMOTE FROM OPERATOR. LOW VOLTAGE CONDUIT RUN FROM EACH CONTROLLER TO OPERATOR BY ELECTRICAL CONTRACTOR.

- 3. DOORS, FRAMES AND HARDWARE BY OTHERS.
- 4. 32" CLEAR DOOR OPENING REQUIRED TO MEET A.D.A. REQUIREMENTS.
- 5. DOORS MUST BE NON-LATCHED FOR PROPER OPERATION.
- 6. OPERATOR CAN BE CONFIGURED TO MEET ANSI STANDARDS A156.10 & ANSI A156.19