

****				
TN	D	W		Y <sub>®</sub>
بال				M

## IMOTION® TN 110 IN-FLOOR SWING DOOR OPERATOR FLUSH MOUNT BOX

AUTOMATIC SINGLE DOOR LH INSWING CENTER PIVOT W/ BREAKAWAY APPLICATION

JOB NAME:	DATE:	
DOOR LOCATION:	DOOR NO:	SHEETOF





OPERATOR AND FLOOR BOX TOP VIEW


## OPTION B

- EXTENDED SHAFT
- SPECIAL REMOVABLE COVER BOX FOR FLOOR COVERING INSTALLATION
- MAX. FLOOR COVERING = 1/2"


PIT DIMENSION


19 3/4"L x 17 3/4"W x 6 7/8"D

FLOOR BOX - OPTION B




- Concrete or Finished Floor
- Weep Drain Required
- Possible Electrical Feed






## FRONT SECTION



CENTER PIVOT

END SECTION B-B



REFER TO THRESHOLD DETAIL DRAWING FOR DISTANCE FROM BOTTOM OF DOOR SHOE TO FINISHED FLOOR

## NOTES:

- 1. DETAILS NOT TO SCALE.
- 2. ELECTRICAL REQUIREMENTS:

  120VAC, 15AMP MIN. TO EACH CONTROLLER LOCATED REMOTE FROM OPERATOR. LOW

  VOLTAGE CONDUIT RUN FROM EACH CONTROLLER TO OPERATOR BY ELECTRICAL CONTRACTOR.
- 3. DOORS, FRAMES AND HARDWARE BY OTHERS.4. 32" CLEAR DOOR OPENING REQUIRED TO MEET A.D.A. REQUIREMENTS.
- 5. DOORS MUST BE NON-LATCHED FOR PROPER OPERATION.
- 6. OPERATOR CAN BE CONFIGURED TO MEET ANSI STANDARDS A156.10 & ANSI A156.19