


TN	R	W		Ye
رب د ا				

IMOTION® TN 110 IN-FLOOR SWING DOOR OPERATOR FLUSH MOUNT BOX

PAIR INSWING CENTER PIVOT w/ BREAKAWAY APPLICATION AUTOMATIC

_DATE: _____ JOB NAME: DOOR NO: _____ DOOR LOCATION: __ SHEET__OF_







OPERATOR AND FLOOR BOX TOP VIEW

- OPTION B - EXTENDED SHAFT
- SPECIAL REMOVABLE COVER BOX FOR FLOOR COVERING INSTALLATION
- MAX. FLOOR COVERING = 1/2"
- <u>PIT DIMENSION</u> 19 3/4"L x 17 3/4"W x 6 7/8"D

DIRECTION OF


PLAN







FLOOR BOX - OPTION B

FRONT SECTION







REFER TO THRESHOLD DETAIL DRAWING FOR DISTANCE FROM BOTTOM OF DOOR SHOE TO FINISHED FLOOR

NOTES:

- 1. DETAILS NOT TO SCALE.
- 2. ELECTRICAL REQUIREMENTS:

Concrete or Finished Floor Weep Drain Required

Possible Electrical Feed

- 120VAC, 15AMP MIN. TO EACH CONTROLLER LOCATED REMOTE FROM OPERATOR. LOW VOLTAGE CONDUIT RUN FROM EACH CONTROLLER TO OPERATOR BY ELECTRICAL CONTRACTOR.
- 3. DOORS, FRAMES AND HARDWARE BY OTHERS.
- 4. 32" CLEAR DOOR OPENING REQUIRED TO MEET A.D.A. REQUIREMENTS.
- 5. DOORS MUST BE NON-LATCHED FOR PROPER OPERATION.
- 6. OPERATOR CAN BE CONFIGURED TO MEET ANSI STANDARDS A156.10 & ANSI A156.19