


CAUTION

MOLDED SEALANT POCKETS MUST BE USED IN CONJUNCTION WITH RAIN HOODS FOR PROJECTS WITH 25 AND 30-YEAR WARRANTIES.



## DIMENSIONS

		cm			cm	
(A)	1"	2.5	MIN.	(B)	2"	5
						MIN.

## NOTES:

- TEMPERATURE OF THE PIPE PENETRATION MUST NOT EXCEED 140°F (60°C) WHEN USING PVC AND 160°F (71°C) WHEN USING TPO FLASHING.
- WHEN USING THERMOPLASTIC MEMBRANE/MOLDED SEALANT POCKET, APPLY A THIN COAT OF TPO/PVC PRIMER TO THE INSIDE AND AROUND THE TOP RIM OF THE POCKET, TO THE DECK MEMBRANE ENCLOSED BY THE POCKET AND TO THE PENETRATION USING A SMALL PAINT BRUSH.
- ONE-PART SEALANT MUST COMPLETELY FILL MOLDED SEALANT POCKET TO PREVENT PONDING OF WATER.
- PIPE CLUSTERS MUST HAVE MINIMUM 1" (2.5cm) CLEARANCE BETWEEN PENETRATIONS.

PLACE MOLDED TPO/PVC SEALANT POCKET AROUND PENETRATION AND OVERLAP THE TWO SECTIONS

