


## NOTES:

1. ALL OUTSIDE AND INSIDE CORNERS REQUIRE TWO COMPLETE CORNER APPLICATIONS OF QUICK-APPLIED UNCURED EPDM FLASHING AS PER DETAILS VGC-15.4A OR VGC-15.7A.
2. ROOF MEMBRANE SHALL BE LOOSE-LAID OVER THE EXPANSION JOINT SUPPORT OR SPONGE TUBING.
3. WIDTH OF JOINT SHALL BE A MINIMUM OF 3/4" (2cm) AND MAXIMUM 2" (5cm) WHEN VERSICO EXPANSION JOINT SUPPORT IS USED.
4. USE DETAIL VGC-2.3 FOR EPDM MEMBRANE SPLICES AT ANGLE CHANGES.
5. HPX FASTENERS AND POLYMER SEAM PLATES ARE REQUIRED ON MECHANICALLY FASTENED SYSTEMS OVER STEEL DECKS.
6. MAXIMUM 6" (15cm) FASTENER SPACING FOR WARRANTY WIND SPEEDS GREATER THAN 90 MPH OR WARRANTIES EXCEEDING 20 YEARS.

MAXIMUM WARRANTY: 30 YEARS

DECK-TO-WALL  
EXPANSION JOINTTHERMOSET  
ROOFING SYSTEM

VGC-3.2