


DIMENSIONS		cm	
(A)	3"	7.5	APPROX.
(B)	1/8"	0.5	MIN.
	1/2"	1.5	MAX.

NOTES:


1. LENGTH OF ROD STOCK IS LIMITED TO 4' (1.2m). USE INDIVIDUAL SECTIONS OF ROD STOCK FOR LONGER DIMENSIONS.
2. MEMBRANE SPLICES SHALL INCORPORATE 6" (15cm) WIDE QA SEAM TAPE FOR PROJECTS WITH 25 and 30-YEAR WARRANTIES.
3. WHEN METAL FLANGE IS ON TOP OF MEMBRANE USE DETAIL VGC-15.6 (20 YEAR) OR VGC-15.7A (25/30 YEAR) TO ACHIEVE SUFFICIENT COVERAGE AT THE CORNERS.
4. DETAIL IS NOT ACCEPTABLE FOR VIBRATING ROOF TOP UNITS.



MAXIMUM WARRANTY: 30 YEARS



SELF-FLASHING CURB

THERMOSET
ROOFING SYSTEM

VGC-5.4