

DIMENSIONS	cm	
(A)	3'-6"	110 MIN.
	4'-6"	140 MAX.
(B)	12" O.C.	30 MAX.


NOTES:

1. RIDGE MEMBRANE ATTACHMENT IS ONLY REQUIRED WHEN ROOF SLOPE EXCEEDS 3" TO THE HORIZONTAL FOOT (7.5cm/30cm).
2. REINFORCED EPDM MEMBRANE SHALL BE INSTALLED PARALLEL WITH RIDGE LINE (WITH MEMBRANE CENTERED OVER THE RIDGE LINE) AS SHOWN.
3. FOR PROPER MEMBRANE ATTACHMENT AND SPLICING, REFER TO APPLICABLE VGMA-2 DETAIL.
4. REFER TO VERSICO SPECIFICATIONS FOR REQUIRED NUMBER OF PERIMETER SHEETS, SHEET WIDTH AND MEMBRANE FASTENING DENSITY.
5. HPX FASTENERS AND POLYMER SEAM PLATES ARE REQUIRED OVER STEEL DECKS.
6. AS AN OPTION, 9" (23cm) WIDE QUICK APPLIED RTS MAY BE USED BENEATH EPDM FIELD SHEETS FOR PERIMETER SECUREMENT.

MAXIMUM WARRANTY: 30 YEARS



RIDGE MEMBRANE
ATTACHMENT



MECHANICALLY
ATTACHED EPDM

VGMA-22