

PVC ONLY
(NOT FOR TPO)




DIMENSIONS	mm	
A 6"	152	
B 8'-0"	2438	MAX.
C 12" O.C.	305	MAX.

NOTES:

1. IN ADDITION TO ADHESIVE, VERTICAL OR HORIZONTAL MEMBRANE SECUREMENT IS REQUIRED.
2. INSTALL VERSIFLEX PVC MEMBRANE HORIZONTALLY AS SHOWN WITH LENGTH PARALLEL TO THE BASE OF THE WALL.
3. ADDITIONAL SECUREMENT IS NOT REQUIRED WHEN FLASHING TERMINATION IS 48" (1219mm) OR LESS.



PARAPET FLASHING > 48" (1200mm) - VERTICAL SECUREMENT

 → PVC MEMBRANE
 → APPROVED SUBSTRATE
 → SEE NOTE(S)

THERMOPLASTIC ROOFING SYSTEM

TPC-12.4