



NOTES:

1. FASTEN COATED METAL FLASHING TO WOOD NAILERS USING 1-1/2" (38mm) MIN. RING SHANK NAILS SPACED 6" (152mm) ON CENTER AND STAGGERED APPROX. 1/2" (13mm).
2. REFER TO THERMOPLASTIC TPC-15.3 DETAIL FOR FLASHING VERTICAL JOINTS IN COATED METAL.



OUTSIDE CORNER WITH COATED METAL WALL FLASHING

→ THERMOPLASTIC REINFORCED MEMBRANE
 → APPROVED SUBSTRATE
 → SEE NOTE(S)

THERMOPLASTIC ROOFING SYSTEM

TPC-15.6