





DIMENSIONS	mm	
(A) 2-1/4"	57	MIN.

NOTE:

1. WHEN USING 60 OR 80-MIL MEMBRANE, APPLY A 4-1/2" (114mm) DIAMETER "T-JOINT" COVER AT ALL FIELD SPLICE INTERSECTIONS.
2. APPROXIMATELY 1/8" (3mm) DIAMETER BEAD OF CUT-EDGE SEALANT IS REQUIRED ON CUT EDGES OF REINFORCED TPO MEMBRANE AND RECOMMENDED ON CUT EDGES OF VERSIFLEX PVC MEMBRANE.



**MEMBRANE SPLICE**

 → THERMOPLASTIC REINFORCED MEMBRANE  
 → APPROVED SUBSTRATE  
 → SEE NOTE(S)

THERMOPLASTIC ROOFING SYSTEM

**TPC-2.0**