


880 WALL GUIDE NO SPLICE										
BUILD HEIGHT (FT)	BUILD HEIGHT (IN)	WALL GUIDE HEIGHT (IN)	NUMBER OF SLOTS	SLOT 1	SLOT 2	SLOT 3	SLOT 4	SLOT 5	SLOT 6	SLOT 7
5	60	79	4	2.0	36.5	71.0	77.0			
5.5	66	85	5	2.0	21.5	41.0	77.0	83.0		
6	72	91	5	2.0	24.5	47.0	83.0	89.0		
6.5	78	97	5	2.0	27.5	53.0	89.0	95.0		
7	84	103	5	2.0	30.5	59.0	95.0	101.0		
7.5	90	109	5	2.0	33.5	65.0	101.0	107.0		
8	96	115	5	2.0	36.5	71.0	107.0	113.0		
8.5	102	121	6	2.0	21.5	41.0	77.0	113.0	119.0	
9	108	127	6	2.0	24.5	47.0	83.0	119.0	125.0	
9.5	114	133	6	2.0	27.5	53.0	89.0	125.0	131.0	
10	120	139	6	2.0	30.5	59.0	95.0	131.0	137.0	
10.5	126	145	6	2.0	33.5	65.0	101.0	137.0	143.0	
11	132	151	6	2.0	36.5	71.0	107.0	143.0	149.0	
11.5	138	157	7	2.0	21.5	41.0	77.0	113.0	149.0	155.0
12	144	163	7	2.0	24.5	47.0	83.0	119.0	155.0	161.0



NO SPLICE JAMB DETAIL
SHOWING 6 SLOTS

ADV-X

880 FLEXIBLE BOTTOM INTERIOR HIGH SPEED FABRIC DOOR		
PROJECT		
ARCHITECT		
CONTRACTOR		
DISTRIBUTOR		
PLANT		
DIST. DWG. NO.	DATE:	
SHEET 2 OF 2	BY:	