


889 WALL GUIDE NO SPLICE 16" O.C.																							
BUILD HEIGHT	BUILD HEIGHT (IN)	STANDARD WALL GUIDE HEIGHT (IN)	LARGE WALL GUIDE HEIGHT (IN)	NUMBER OF SLOTS	SLOT 1	SLOT 2	SLOT 3	SLOT 4	SLOT 5	SLOT 6	SLOT 7	SLOT 8	SLOT 9	SLOT 10	SLOT 11	SLOT 12	SLOT 13	SLOT 14	SLOT 15	SLOT 16	SLOT 17	SLOT 18	SLOT 19
5	60	91.5		10	3.0	15.00	27.00	43.00	50.75	58.50	64.50	68.88	83.63	88.00									
5.5	66	97.5		10	3.0	19.00	35.00	51.00	57.75	64.50	70.50	74.88	89.63	94.00									
6	72	103.5		11	3.0	14.00	25.00	41.00	57.00	63.75	70.50	76.50	80.88	95.63	100.00								
6.5	78	109.5		11	3.0	17.00	31.00	47.00	63.00	69.75	76.50	82.50	86.88	101.63	106.00								
7	84	115.5		12	3.0	12.00	21.00	37.00	53.00	69.00	75.75	82.50	88.50	92.88	107.63	112.00							
7.5	90	121.5		12	3.0	15.00	27.00	43.00	59.00	75.00	81.75	88.50	94.50	98.88	113.63	118.00							
8	96	127.5		12	3.0	18.00	33.00	49.00	65.00	81.00	87.75	94.50	100.50	104.88	119.63	124.00							
8.5	102	133.5		13	3.0	13.00	23.00	39.00	55.00	71.00	87.00	93.75	100.50	106.50	110.88	125.63	130.00						
9	108	139.5		13	3.0	16.00	29.00	45.00	61.00	77.00	93.00	99.75	106.50	112.50	116.88	131.63	136.00						
9.5	114	145.5		13	3.0	19.00	35.00	51.00	67.00	83.00	99.00	105.75	112.50	118.50	122.88	137.63	142.00						
10	120	151.5		14	3.0	14.00	25.00	41.00	57.00	73.00	89.00	105.00	111.75	118.50	124.50	128.88	143.63	148.00					
10.5	126	157.5		14	3.0	17.00	31.00	47.00	63.00	79.00	95.00	111.00	117.75	124.50	130.50	134.88	149.63	154.00					
11	132	163.5		15	3.0	12.00	21.00	37.00	53.00	69.00	85.00	101.00	117.00	123.75	130.50	136.50	140.88	155.63	160.00				
11.5	138	169.5		15	3.0	15.00	27.00	43.00	59.00	75.00	91.00	107.00	123.00	129.75	136.50	142.50	146.88	161.63	166.00				
12	144	175.5		15	3.0	18.00	33.00	49.00	65.00	81.00	97.00	113.00	129.00	135.75	142.50	148.50	152.88	167.63	172.00				
12.5	150	181.5		16	3.0	13.00	23.00	39.00	55.00	71.00	87.00	103.00	119.00	135.00	141.75	148.50	154.50	158.88	173.63	178.00			
13	156	187.5		16	3.0	16.00	29.00	45.00	61.00	77.00	93.00	109.00	125.00	141.00	147.75	154.50	160.50	164.88	179.63	184.00			
13.5	162	193.5		16	3.0	19.00	35.00	51.00	67.00	83.00	99.00	115.00	131.00	147.00	153.75	160.50	166.50	170.88	185.63	190.00			
14	168	199.5		17	3.0	14.00	25.00	41.00	57.00	73.00	89.00	105.00	121.00	137.00	153.00	159.75	166.50	172.50	176.88	191.63	196.00		
14.5	174	205.5		17	3.0	17.00	31.00	47.00	63.00	79.00	95.00	111.00	127.00	143.00	159.00	165.75	172.50	178.50	182.88	197.63	202.00		
15	180	211.5		18	3.0	12.00	21.00	37.00	53.00	69.00	85.00	101.00	117.00	133.00	149.00	165.00	171.75	178.50	184.50	188.88	203.63	208.00	
15.5	186		223.5	18	3.0	12.00	27.00	43.00	59.00	75.00	91.00	107.00	123.00	139.00	155.00	171.00	177.75	184.50	190.50	194.88	215.63	220.00	
16	192		229.5	19	3.0	7.00	17.00	33.00	49.00	65.00	81.00	97.00	113.00	129.00	145.00	161.00	177.00	183.75	190.50	196.50	200.88	221.63	226.00
16.5	198		235.5	19	3.0	16.00	29.00	45.00	61.00	77.00	93.00	109.00	125.00	141.00	157.00	173.00	189.00	195.75	202.50	208.50	212.88	227.63	232.00



889 WALL GUIDE SPLICE 16" O.C.																												
BUILD HEIGHT (FT)	BUILD HEIGHT (IN)	BOTTOM WALL GUIDE HEIGHT (IN)	TOP WALL GUIDE HEIGHT (IN)	NUMBER OF SLOTS	SLOT 1	SLOT 2	SLOT 3	SLOT 4	SLOT 5	SLOT 6	SLOT 7	SLOT 8	SLOT 9	SLOT 10	SLOT 11	SLOT 12	SLOT 13	SLOT 14	SLOT 15	SLOT 16	SLOT 17	SLOT 18	SLOT 19	SLOT 20	SLOT 21	SLOT 22	SLOT 23	SLOT 24
17	204	122	119.5	21	3.00	13.00	23.00	39.00	55.00	71.00	87.00	103.00	119.00	125.00	141.00	157.00	173.00	189.00	195.75	202.50	208.50	212.88	233.63	238.00				
17.5	210	128	119.5	21	3.00	16.00	29.00	45.00	61.00	77.00	93.00	109.00	125.00	131.00	147.00	163.00	179.00	195.00	201.75	208.50	214.50	218.88	239.63	244.00	244.00			
18	216	134	119.5	21	3.00	19.00	35.00	51.00	67.00	83.00	99.00	115.00	131.00	137.00	153.00	169.00	185.00	201.00	207.75	214.50	220.50	224.88	245.63	250.00	250.00			
18.5	222	140	119.5	22	3.00	14.00	25.00	41.00	57.00	73.00	89.00	105.00	121.00	137.00	143.00	159.00	175.00	191.00	207.00	213.75	220.50	226.50	230.88	251.63	256.00	256.00		
19	228	146	119.5	22	3.00	17.00	31.00	47.00	63.00	79.00	95.00	111.00	127.00	143.00	149.00	165.00	181.00	197.00	213.00	219.75	226.50	232.50	236.88	257.63	262.00	262.00		
19.5	234	152	119.5	23	3.00	12.00	21.00	37.00	53.00	69.00	85.00	101.00	117.00	133.00	149.00	165.00	171.00	187.00	203.00	219.00	225.75	232.50	238.50	242.88	263.63	268.00	268.00	
20	240	158	119.5	23	3.00	15.00	27.00	43.00	59.00	75.00	91.00	107.00	123.00	139.00	155.00	161.00	177.00	193.00	209.00	225.00	231.75	238.50	244.50	248.88	269.63	274.00	274.00	
20.5	246	164	119.5	23	3.00	18.00	33.00	49.00	65.00	81.00	97.00	113.00	129.00	145.00	161.00	167.00	183.00	199.00	215.00	231.00	237.75	244.50	250.50	254.88	275.63	280.00	280.00	
21	252	170	119.5	24	3.00	13.00	23.00	39.00	55.00	71.00	87.00	103.00	119.00	135.00	151.00	167.00	173.00	189.00	205.00	221.00	237.00	243.75	250.50	256.50	260.88	281.63	286.00	286.00

ADV-X<sup>®</sup>

COLUMN OF SLOTS CLOSER TO THE OPENING (WITH 16" SPACING) IS USED ON STEEL JAMBS WITH PROVIDED BOLTS TO BE PLACED IN EVERY SINGLE SLOT. IT MAY ALSO BE PLUG-WELDED TO THE JAMB THROUGH THESE SLOTS . WITH E-GUIDE, IT IS ALWAYS 16"SPACING. Z-GUIDES CAN USE BOTH 16" AND 8" SPACING.

888 ADV-X HIGH SPEED METAL DOORS		
PROJECT		
ARCHITECT		
CONTRACTOR		
DEALER		
PLANT		LEWISTOWN
DWG. NO.	DATE:	<b>Wayne Dalton</b> COMMERCIAL DOORS
SHEET 3 OF 4	BY:	