




MODEL	STANDARD MAX. VALUES	
	WIDTH	HEIGHT
453	22' 2"	20' 1"



SECTION B-B



SECTION A-A

OPTIONS	
OPENING WIDTH	
OPENING HEIGHT	
DOOR TRACK SIZE	☐ 2" ☐ 3"
GLAZING OPTIONS	☐ DSB GLASS ☐ ACRYLIC ☐ TEMPERED GLASS ☐ CLEAR POLYCARBONATE ☐ MULTI-WALL POLYCARBONATE ☐ WIRE GLASS ☐ LOW E ☐ POLYCARBONATE ☐ LAMINATE

COMPONENT	MATERIAL	OPERATION	NOTES:
MATERIAL	6063-T6 ALUMINUM	MANUAL PULL ROPE	- WARRANTY: 1-YEAR LIMITED; 3-YEAR LIMITED POWDER COAT FINISH
HINGES/FIXTURES	GALVANIZED STEEL		
LOCK	GALVANIZED, INTERIOR-MOUNTED		
WEATHERSTRIP	FLEXIBLE PVC		

ALUMINUM
SECTIONAL

453 ALUMINUM GLASS DOOR

DWG. NO.	DATE:	
SHEET	BY:	