


**XYPEX PROJECT SPECIFICATIONS & SCHEMATIC DRAWINGS**  
**FERRO-CEMENT BOAT/CAISSON/FLOATING DOCK**



----- CONCENTRATE SLURRY COAT

- - - - - MODIFIED SLURRY COAT

- ① APPLY ONE SLURRY COAT OF XYPEX CONCENTRATE TO HULL EXTERIOR, GUNWHALES, AND ALL EXTERIOR DECKS AT THE RATE OF 1.5 LB./SQ. YD. (0.8 KG/M<sup>2</sup>)
- ② APPLY ONE COAT OF XYPEX MODIFIED TO INTERIOR SURFACE OF HULL AT THE RATE OF 1.5 LB./SQ. YD. (0.8 KG/M<sup>2</sup>)

**NOTE: IN THE CASE OF SEALED, HOLLOW-CORE CAISSONS, STEP 2 IS ELIMINATED AND THE CONCENTRATE SLURRY COAT IN STEP 1 SHOULD EXTEND OVER ENTIRE EXTERIOR OF UNIT.**

**SCHEMATIC DIAGRAM SHOWS XYPEX APPLICATION ONLY AND DOES NOT DEPICT THE STANDARD REQUIREMENTS FOR WATERSTOPS OR EXPANSION JOINT SEALANTS.**

**THE SPECIFIER CAN CONSIDER THE ALTERNATIVE USE OF XYPEX DRY SHAKE OR XYPEX ADMIX, WHERE APPLICABLE.**

**REFER TO STANDARD SPECIFICATIONS FOR FURTHER INFORMATION.**