SCS Global Services does hereby certify that an independent assessment has been conducted on behalf of:

MAPEI Corporation

1144 E Newport Center Drive, Deerfield Beach, FL, United States

For the following product(s):

See Addendum

The product(s) meet(s) all of the necessary qualifications to be certified for the following claim(s):

Indoor Advantage™ Gold

Indoor Air Quality Certified to SCS-EC10.3-2014 v4.0

Conforms to the CDPH/EHLB Standard Method (CA 01350) v1.2-2017 (effective January 2017) for the school classroom, private office, and single-family residence parameters when modeled as Flooring. Also, SCAQMD Rule 1113 - Architectural Coatings (September 2013); European Decopaint (2004/42/EC); Canadian VOC Concentration Limits for Architectural Coatings (SOR/2009-264: April 16, 2014); Hong Kong Air Pollution Control (VOC) Regulation.

Standard Product Application Amount: 37.2 m² per gallon

Measured Concentration of Total Volatile Organic Compounds (TVOC): Less than/equal to 0.5 mg/m3 (in compliance with CDPH/EHLB Standard Method v1.2-2017)

Methylene Chloride and Perchloroethylene are not intentionally added to certified products.

Registration # SCS-IAQ-06040

Valid from: March 23, 2022 to March 22, 2023







Transcy Mather Kam

Stanley Mathuram, PE, Executive Vice President SCS Global Services 2000 Powell Street, Ste. 600, Emeryville, CA 94608 USA

Certification Addendum

MAPEI Corporation

Certification: Registration # SCS-IAQ-06040 | Valid from: March 23, 2022 to March 22, 2023

Indoor Advantage™ Gold

Addendum Conformance:

Addendum Indoor Air Quality Certified to SCS-EC10.3-2014 v4.0

Conforms to the CDPH/EHLB Standard Method (CA 01350) v1.2-2017 (effective January 2017) for the school classroom, private office, and single-family residence parameters when modeled as Flooring. Also, SCAQMD Rule 1113 - Architectural Coatings (September 2013); European Decopaint (2004/42/EC); Canadian VOC Concentration Limits for Architectural Coatings (SOR/2009-264: April 16, 2014); Hong Kong Air Pollution Control (VOC) Regulation. Standard Product Application Amount: 37.2 m² per gallon. Measured Concentration of Total Volatile Organic Compounds (TVOC): Less than/equal to 0.5 mg/m3 (in compliance with CDPH/EHLB Standard Method v1.2-2017)

Methylene Chloride and Perchloroethylene are not intentionally added to certified products.

Products: Architectural Coatings:

Admixtures: Mapecure SRA, Planicrete AC, Planicrete LA, Planicrete UA, Planitop Accelerator

Wood Base Coats: Ultracoat Base One, Ultracoat Premium Base, Ultracoat Toning Base, Ultracoat Universal Base

Bond Promoting Primer: ECO Prim Grip

Coatings and Sealers: Elastocolor Coat, Elastocolor Flex, Elastocolor Paint, Elastocolor Primer AR, Elastocolor Primer WB, Elastocolor Texture, Mapecoat Deck T, Mapefinish Wet Look, Mapefloor Finish 415 NA, Mapefloor Finish 450, Mapefloor Finish 53 W/L, Mapefloor Finish 54 W/S, Mapefloor Finish 58 W, Mapefloor PU 400 FC, Mapefloor PU Primer, Planiseal CR1, Planiseal HG, Planiseal LVB, Planiseal Traffic Coat, Planiseal Traffic Coat FS, Planiseal WR, Planiseal WR 100, Planiseal WR 40, Primer SN, Primer SN Fast

Corrosion Protection: Mapefer 1K, Mapeshield CI 100, Planibond 3C

Crack Isolation and Sound Reduction: Mapelastic CI

CRS Waterproofing: Mapeflex P2 NS, Mapelastic, Planiseal 288, Planiseal 88, Resfoam HB 45, Resfoam HBA 45,

Resfoam HBA 75, Resfoam HL 35, Resfoam PF, Resfoam SS 75

Cure and Seals: Mapecrete Film, Mapecure AP, Mapecure CS, Mapecure DR, Mapecure UV



Certification Addendum

MAPEI Corporation

Certification: Registration # SCS-IAQ-06040 | Valid from: March 23, 2022 to March 22, 2023

Indoor Advantage™ Gold

Addendum Conformance:

Addendum Indoor Air Quality Certified to SCS-EC10.3-2014 v4.0

Conforms to the CDPH/EHLB Standard Method (CA 01350) v1.2-2017 (effective January 2017) for the school classroom, private office, and single-family residence parameters when modeled as Flooring. Also, SCAQMD Rule 1113 - Architectural Coatings (September 2013); European Decopaint (2004/42/EC); Canadian VOC Concentration Limits for Architectural Coatings (SOR/2009-264: April 16, 2014); Hong Kong Air Pollution Control (VOC) Regulation. Standard Product Application Amount: 37.2 m² per gallon. Measured Concentration of Total Volatile Organic Compounds (TVOC): Less than/equal to 0.5 mg/m3 (in compliance with CDPH/EHLB Standard Method v1.2-2017)

Methylene Chloride and Perchloroethylene are not intentionally added to certified products.

Products: **Decorative Toppings:** Ultratop, Ultratop PC, Ultratop SP

Densifiers: Mapecrete Hard FS, Mapecrete Hard LI, Mapecrete Hard SB, Mapecrete Hard SI

Sealants and Joint Fillers: Mapeflex EMC-1, Mapeflex P2 SL, Mapeflex Joint Filler PO 95/100, Mapeflex Joint Filler EP

90/50, Mapeflex PU40, Mapeflex PU50 SL

Wood Finishes: Ultracoat Aqua Plus, Ultracoat Easy, Ultracoat Easy Plus, Ultracoat Gym, Ultracoat Gym Pro, Ultracoat

High Traffic

Mastics: Ker 909, Type 1, Ultramastic Eco

Moisture-Vapor Reducing Epoxy & Alkalinity Barrier: Planiseal MVR

Premium Mortar Moisture Control: Planiseal MB

Patching Compounds, Skimcoats & Additives: Mapecem Quickpatch, Planipatch, Planipatch Plus, Planiprep 4 LVT,

Planiprep PSC, Planiprep SC, Tilt Finish

Primers / Self-Leveling: Mapei HM Primer, Mapei SM Primer, Mapei SM Primer Fast, Mapewrap Primer 1, Planibond

EBA, Primer CE, Primer E, Primer L, Primer T, Primer X, Primer WE

Wood Refinishing System: Ultracoat ReNewlt Primer, Ultracoat ReNewlt Remover



Certification Addendum

MAPEI Corporation

Certification: Registration # SCS-IAQ-06040 | Valid from: March 23, 2022 to March 22, 2023

Indoor Advantage™ Gold

Addendum Conformance:

Addendum Indoor Air Quality Certified to SCS-EC10.3-2014 v4.0

Conforms to the CDPH/EHLB Standard Method (CA 01350) v1.2-2017 (effective January 2017) for the school classroom, private office, and single-family residence parameters when modeled as Flooring. Also, SCAQMD Rule 1113 - Architectural Coatings (September 2013); European Decopaint (2004/42/EC); Canadian VOC Concentration Limits for Architectural Coatings (SOR/2009-264: April 16, 2014); Hong Kong Air Pollution Control (VOC) Regulation. Standard Product Application Amount: 37.2 m² per gallon. Measured Concentration of Total Volatile Organic Compounds (TVOC): Less than/equal to 0.5 mg/m3 (in compliance with CDPH/EHLB Standard Method v1.2-2017)

Methylene Chloride and Perchloroethylene are not intentionally added to certified products.

Products:

Self-Leveling Underlayments & Primers: Novoplan 1, Novoplan 2 Plus, Novoplan 710 SL, Novoplan DPL, Novoplan Easy Plus, Novoplan HFL, Novoplan SP, PlaniLevel 360, PlaniLevel 420, PlaniLevel 450, PlaniLevel 500, PlaniLevel 560, Planitex SLF, Self-Leveler Plus, Ultraplan 1 Plus, Ultraplan Easy, Ultraplan Extreme 2, Ultraplan Lite, Ultraplan LSC, Ultraplan M20 Plus

Hardcourt Sports Surfaces: Mapecoat TNS Base Color, Mapecoat TNS Base Gray, Mapecoat TNS Base White, Mapecoat TNS Binder, Mapecoat TNS Finish 1, Mapecoat TNS Line Seal, Mapecoat TNS Line Tex, Mapecoat TNS Primer EPW

Cement Based Flooring System: Mapefloor CPU/MF, Mapefloor CPU/HD, Mapefloor CPU/RT, Mapefloor CPU/COVE, Mapefloor CPU/TC, Mapefloor CPU/SB, Mapecolor Paste, Mapecolor CPU, Mapefloor Finish 630, Mapefloor PU 418 **Resinous Flooring System**: Mapefloor I 900, Mapefloor I 302 SL, Mapefloor I 320 SL Concept, Mapecoat Universal, Mapefloor Compact, Mapecoat I 24

Saturants: MapeWrap 21, MapeWrap 21 TG, MapeWrap 31, MapeWrap 31 Slow Set, MapeWrap 31 T

Waterproofing Membranes: Mapelastic Smart

