

IAPMO RESEARCH AND TESTING, INC.

5001 E. Philadelphia Street, Ontario, CA 91761 • Phone (909) 472-4100 • Fax (909) 472-4244 • www.iapmort.org



IAPMO R&T Product Listing

LEAD FREE

This IAPMO R&T Listing is current as of April 6, 2022

File Number:

6798

Issued To:

MIFAB, INC.

1321 WEST 119TH STREET CHICAGO, IL , United States

Product:

Lead Free Plumbing Products

Products are in compliance with the following standard(s)

Section 1417(d) of the Safe Drinking Water Act, and The lead content requirements of Section 116875 of the California Health & Safety Code

**IAPMO RESEARCH AND TESTING, INC.
CERTIFICATE OF LISTING**

LEAD FREE **Issued To:** MIFAB, INC.
File Number: 6798
Product: Lead Free Plumbing Products

This IAPMO R&T Listing is current as of April 6, 2022

Identification:

Each product shall bear permanent and legible markings to identify the manufacturer. This marking shall be the trade name, trademark, or other mark known to identify the manufacturer. The product shall bear the appropriate IAPMO R&T certification mark. The product may also bear either "Lead Free" or "Low Lead" above or in close proximity to the IAPMO R&T certification mark.

Characteristics:

Products may include any pipe, pipe fitting, solder, flux, or other plumbing products providing water for human consumption. Products listed below are to be installed in accordance with the manufacturer's instruction. These products have been verified with weighted average lead content $\leq 0.25\%$; Solder and flux lead content $\leq 0.2\%$.

Products listed on this certificate have been tested by an IAPMO R&T recognized laboratory. This recognition has been granted based upon the laboratory's compliance to the applicable requirements of ISO/IEC 17025.

Models

Model Number	Description
F1002-5-3	Floor Drain with S/S Strainer
F1003-5-3	Floor Drain with S/S Strainer
F1004-5-3	Floor Drain with S/S Strainer
F1005-5-3	Floor Drain with S/S Strainer
F1006-5-3	Floor Drain with S/S Strainer
M1-500-MPB	
M2-500NPB	
MI-100-10	

Model Number	Description
MI-100-15	
MI-100-20	
MI-100-25	
MI-100-30	
MI-100-35	
MI-100-5	
MI-TEMP-NPB	Automatic Pressure Balance Valve
MR-500-NPB	

Brand: Beeco

Model Number
ASVB.25-B-LL
ASVB.25-CP-LL
ASVB.50-B-LL
ASVB.50-CP-LL
ASVB.75-B-LL
ASVB.75-CP-LL
ASVB.375-B-LL
ASVB.375-CP-LL

Model Number	Description
DC 1/2 NPT X 1/2 NPT-LL	1/2" IPS x 1/2" IPS Connections, In Line Double Check Valve, Low Lead
DC 3/4 NPT X 3/4 NPT-LL	3/4" IPS x 3/4" IPS Connections, In Line Double Check Valve, Low Lead
DC 1 NPT X 1 NPT-LL	1" IPS x 1" IPS Connections, In Line Double Check Valve, Low Lead
DC 1/2 SWT X 1/2 NPT-LL	1/2" Sweat x 1/2" IPS Connections, In Line Double Check Valve, Low Lead
DC 3/4 SWT X 3/4-NPT-LL	3/4" Sweat x 3/4" IPS Connections, In Line Double Check Valve, Low Lead
DC 1 SWT X 1 NPT-LL	1" Sweat x 1" IPS Connections, In Line Double Check Valve, Low Lead
PRV2.00-DU-IPS-C-LL	2" IPS Connections, Pressure Reducing Valve, Double Union, Compact Design, Low Lead
PRV2.00-DU-SWT-C-LL	2" Sweat Connections, Pressure Reducing Valve, Double Union, Compact Design, Low Lead
PRV1.50-DU-IPS-C-LL	1-1/2" IPS Connections, Pressure Reducing Valve, Double Union, Compact Design, Low Lead
PRV1.50-DU-SWT-C-LL	1-1/2" Sweat Connections, Pressure Reducing Valve, Double Union, Compact Design, Low Lead
PRV1.25-DU-IPS-C-LL	1-1/4" IPS Connections, Pressure Reducing Valve, Double Union, Compact Design, Low Lead
PRV1.25-DU-SWT-C-LL	1-1/4" Sweat Connections, Pressure Reducing Valve, Double Union, Compact Design, Low Lead

ModelNumber	Description
FDC.50-QT-LL	1/2" IPS x 1/2" IPS connections, Backflow Preventer (Double Check)
FDC.75-QT-LL	3/4" IPS x 3/4" IPS connections, Backflow Preventer (Double Check)
FDC1.00-QT-LL	1" IPS x 1" IPS connections, Backflow Preventer (Double Check)
FDC1.25-QT-LL	1-1/4" IPS x 1-1/4" IPS connections, Backflow Preventer (Double Check)
FDC1.50-QT-LL	1-1/2" IPS x 1-1/2" IPS connections, Backflow Preventer (Double Check)
FDC10.00-NRS	10" Double Check Backflow Preventer with NRS Gate Valves
FDC10.00-OSY	10" Double Check Backflow Preventer with OSY Gate Valves
FDC2.00-QT-LL	2" IPS x 2" IPS connections, Backflow Preventer (Double Check)
FDC2.50-NRS	2-1/2" Double Check Backflow Preventer with NRS Gate Valves

ModelNumber	Description
FDC2.50-OSY	2-1/2" Double Check Backflow Preventer with OSY Gate Valves
FDC3.00-NRS	3" Double Check Backflow Preventer with NRS Gate Valves
FDC3.00-OSY	3" Double Check Backflow Preventer with OSY Gate Valves
FDC4.00-NRS	4" Double Check Backflow Preventer with NRS Gate Valves
FDC4.00-OSY	4" Double Check Backflow Preventer with OSY Gate Valves
FDC6.00-NRS	6" Double Check Backflow Preventer with NRS Gate Valves
FDC6.00-OSY	6" Double Check Backflow Preventer with OSY Gate Valves
FDC8.00-NRS	8" Double Check Backflow Preventer with NRS Gate Valves
FDC8.00-OSY	8" Double Check Backflow Preventer with OSY Gate Valves
FRP 1.00-QT-LL	1" IPS x 1" IPS connections, Reduced Pressure Principle Backflow Preventer
FRP 1.25-QT-LL	1-1/4" IPS x 1-1/4" IPS connections, Reduced Pressure Principle Backflow Preventer
FRP 1.50-QT-LL	1-1/2" IPS x 1-1/2" IPS connections, Reduced Pressure Principle Backflow Preventer
FRP 2.00-QT-LL	2" IPS x 2" IPS connections, Reduced Pressure Principle Backflow Preventer
FRP.50-QT-LL	1/2" IPS x 1/2" IPS connections, Reduced Pressure Principle Backflow Preventer
FRP.75-QT-LL	3/4" IPS x 3/4" IPS connections, Reduced Pressure Principle Backflow Preventer
FRP10.00-NRS	10" Reduced Pressure Zone Backflow Preventer with NRS Gate Valves
FRP10.00-OSY	10" Reduced Pressure Zone Backflow Preventer with OSY Gate Valves
FRP2.50-NRS	2-1/2" Reduced Pressure Zone Backflow Preventer with NRS Gate Valves
FRP2.50-OSY	2-1/2" Reduced Pressure Zone Backflow Preventer with OSY Gate Valves
FRP3.00-NRS	3" Reduced Pressure Zone Backflow Preventer with NRS Gate Valves
FRP3.00-OSY	3" Reduced Pressure Zone Backflow Preventer with OSY Gate Valves
FRP4.00-NRS	4" Reduced Pressure Zone Backflow Preventer with NRS Gate Valves
FRP4.00-OSY	4" Reduced Pressure Zone Backflow Preventer with OSY Gate Valves
FRP6.00-NRS	6" Reduced Pressure Zone Backflow Preventer with NRS Gate Valves
FRP6.00-OSY	6" Reduced Pressure Zone Backflow Preventer with OSY Gate Valves
FRP8.00-NRS	8" Reduced Pressure Zone Backflow Preventer with NRS Gate Valves
FRP8.00-OSY	8" Reduced Pressure Zone Backflow Preventer with OSY Gate Valves
STR.50-IPS-BRZ-LL	1/2" IPS x 1/2" IPS connections, Wye Type Strainer
STR.50-SWT-BRZ-LL	1/2" SWT x 1/2" SWT connections, Wye Type Strainer
STR.75-IPS-BRZ-LL	3/4" IPS x 3/4" IPS connections, Wye Type Strainer
STR.75-SWT-BRZ-LL	3/4" SWT x 3/4" SWT connections, Wye Type Strainer
STR1.00-IPS-BRZ-LL	1" IPS x 1" IPS connections, Wye Type Strainer
STR1.00-SWT-BRZ-LL	1" SWT x 1" SWT connections, Wye Type Strainer
STR1.25-IPS-BRZ-LL	1-1/4" IPS x 1-1/4" IPS connections, Wye Type Strainer
STR1.25-SWT-BRZ-LL	1-1/4" SWT x 1-1/4" SWT connections, Wye Type Strainer
STR1.50-IPS-BRZ-LL	1-1/2" IPS x 1-1/2" IPS connections, Wye Type Strainer
STR1.50-SWT-BRZ-LL	1-1/2" SWT x 1-1/2" SWT connections, Wye Type Strainer
STR2.00-IPS-BRZ-LL	2" IPS x 2" IPS connections, Wye Type Strainer
STR2.00-SWT-BRZ-LL	2" SWT x 2" SWT connections, Wye Type Strainer