

# PURE PERFORMANCE®

INTERIOR PAINT



**ZERO VOC\* & LOW ODOR**  
**PROVIDES A MOLD & MILDEW RESISTANT COATING**  
**PAINT & PRIMER IN ONE**  
**100% ACRYLIC LATEX**

## FEATURES & BENEFITS

- Zero-VOC\* & low odor paint is better for the environment and is ideal for painting occupied rooms
- Paint & primer in one means two coats will cover over most colors as well as a primer and topcoat
- The 100% acrylic latex formula provides overall durability and long-lasting beauty
- Good hiding and coverage allows users to use less paint than traditional zero-VOC\* paints

\*Colorants added to this base paint may increase VOC level significantly depending on color choice.

## CONFORMANCE STANDARDS

0 g/L VOC\* compliant in all regulated areas. Can help earn LEED V4 EQ Low-Emitting Materials Credit. Greenguard Gold Certified – Meets Strict Chemical Emissions Limits. Meets MPI Category: 44, 53, 54, 138, 141, 143, 143 X-Green, 144, 144 X-Green, 147, & 147 X-Green.

Our premium low-odor, zero-VOC\* (volatile organic compounds) interior 100% acrylic latex paint is designed to meet the performance requirements of the institutional, commercial, and residential markets. *Pure Performance* paint & primer in one interior latex is formulated to provide excellent hiding and application properties in addition to low odor, zero-VOC\*, and anti-microbial properties - a mold/mildew resisting component has been incorporated in this paint to make the dry paint film mildew resistant. Ideal for use in occupied areas such as hotel/motel resort properties, nursing homes, homes, schools, government facilities, retail space, office buildings, hospitals, and apartments.

### PPG PURE PERFORMANCE FORMULA FEATURES

	WASHABILITY	SCRUB RESISTANCE	BURNISH RESISTANCE	TOUCH-UP
<i>PURE PERFORMANCE</i>	★★★★☆	★★★★☆	★★★★☆	★★★★★
LEADING STORE COMPETITOR	★★★★☆	★★★☆☆	★★★★☆	★★★★☆
LEADING DEALER COMPETITOR	★★★★☆	★★★★☆	★★★★☆	★★★★★

\*Results are from internal and external testing and may vary slightly.



# PURE PERFORMANCE®

PINTURA PARA INTERIORES

**CERO CONTENIDO DE COMPUESTOS ORGÁNICOS VOLÁTILES\* (COV) Y OLOR SUAVEALTO OCULTAMIENTO OFRECE UN REVESTIMIENTO RESISTENTE AL MOHO Y A LOS HONGOS PINTURA E IMPRIMADOR EN UNO 100 % LÁTEX ACRÍLICO**

## CARACTERÍSTICAS Y BENEFICIOS

- La pintura con cero contenido de compuestos orgánicos volátiles\* (COV) y olor suave es mejor para el medio ambiente y es ideal para pintar habitaciones ocupadas
- Pintura e imprimador en uno significa que dos capas cubren la mayoría de los colores, así como una imprimación y una capa de acabado
- La fórmula de látex 100% acrílico proporciona durabilidad general y belleza duradera
- El buen ocultamiento y cobertura permite a los usuarios usar menos pintura que las pinturas tradicionales con cero compuestos orgánicos volátiles\* (COV)

## ESTÁNDARES DE CONFORMIDAD

0 g/l Cumple con los COV\* en todas las áreas reguladas. Puede ayudar a ganar Crédito por Materiales de Baja Emisión LEED V4 EQ. Certificación Gold Greenguard: Cumple con los límites estrictos de emisiones químicas. Cumple con la categoría MPI: 44, 53, 54, 138, 141, 143, 143 X-Green, 144, 144 X-Green, 147, & 147 X-Green.

Nuestra pintura de látex acrílico premium de bajo olor y cero COV\* (compuestos orgánicos volátiles) para interiores está diseñada para cumplir con los requisitos de rendimiento de los mercados institucionales, comerciales y residenciales. *Pure Performance Paint & Primer in One Interior Latex* está formulado para proporcionar excelentes propiedades de ocultamiento y aplicación, además de propiedades de bajo olor, cero COV\*, y propiedades antimicrobianas - un componente resistente al moho y a los hongos ha sido incorporado en esta pintura para hacer que la película de pintura seca sea resistente al moho. Ideal para uso en áreas ocupadas como propiedades de hoteles y moteles resort, residencias de ancianos, hogares, escuelas, instalaciones gubernamentales, locales comerciales, edificios de oficinas, hospitales y apartamentos.

PPG PURE PERFORMANCE CARACTERÍSTICAS DE LA FÓRMULA				
	FACILIDAD DE LAVADO	RESISTENCIA A LA ABRASIÓN	RESISTENCIA AL BRUÑIDO	RETOQUE
PURE PERFORMANCE	★★★★☆	★★★★☆	★★★★☆	★★★★★
COMPETIDOR LÍDER EN TIENDAS	★★★★☆	★★★☆☆	★★★★☆	★★★★☆
COMPETIDOR LÍDER ENTRE DISTRIBUIDORES	★★★★☆	★★★☆☆	★★★★☆	★★★★★

\*Los resultados son de pruebas internas y externas y pueden variar ligeramente.

## AVAILABLE SHEENS BRILLOS DISPONIBLES

CODE CÓDIGO	BASE BASE	SIZES TAMAÑOS
<b>FLAT MATE</b>		
9-100	Pure White Blanco puro	1s, 5s
9-110XI	White & Pastel Blanco y pastel	Qts, 1s, 5s
9-120	Midtone Tono medio	Qts, 1s, 5s
9-140	Ultra-Deep Ultra profundo	Qts, 1s
<b>EGGSHELL PORCELANA TRANSLÚCIDA</b>		
9-300XI	Pure White Blanco puro	1s, 5s
9-310XI	White & Pastel Blanco y pastel	Qts, 1s, 5s
9-320	Midtone Tono medio	Qts, 1s, 5s
9-340	Ultra-Deep Ultra profundo	Qts, 1s

CODE CÓDIGO	BASE BASE	SIZES TAMAÑOS
<b>SEMI-GLOSS SEMIBRILLANTE</b>		
9-500	Pure White Blanco puro	1s, 5s
9-510XI	White & Pastel Blanco y pastel	Qts, 1s, 5s
9-520	Midtone Tono medio	Qts, 1s, 5s
9-540	Ultra-Deep Ultra profundo	Qts, 1s
<b>PRIMER IMPRIMADOR</b>		
9-900	White Blanco	1s, 5s

Visit [ppgpaints.com](http://ppgpaints.com) for more information.

PPG Architectural Finishes, Inc. • 400 Bertha Lamme Drive • Cranberry Twp, PA 16066  
 Technical Service: 1-800-441-9695 • Architect/Specifier: 1-888-774-7732

© 2019 PPG Industries, Inc. All Rights Reserved. The PPG Logo is a registered trademark of PPG Industries Ohio, Inc.  
 Pure Performance is a registered trademark of PPG Architectural Finishes, Inc. ST466584

