

AP-5010

RECESSED ACCESS DOOR

for acoustical plaster walls and ceilings

Application

- Designed for use in acoustical plaster walls and ceilings

Product Features

- Door is recessed 5/8" and is lined with self-furring lath
- Expansion casing bead with 3" wide galvanized lath
- Concealed, pivoting rod type hinge

AP-5010 Access Door Specifications:

Material: Steel

Door: 16 gauge recessed 5/8" lined with self-furring galvanized lath

Door Frame: 14 gauge expansion casing bead with 3" wide galvanized lath, recessed 3/4" to receive plaster

Hinge: Concealed, pivoting rod type. (For wall applications, a continuous exposed piano hinge is suggested.)

Standard Latch: Flush to surface, Slotted Screwdriver Cam Latch

Optional Latches/Locks: Cylinder lock and key, allen head cam latch, spanner head cam latch

Finish: Baked White Prime Coat

(Additional finish paint is recommended for superior corrosion resistance)



AP-5010 STANDARD SIZES

(other sizes available upon request)

Nominal Door Size W&H		Latches	Weight per Door	
Inches	mm		lbs.	kg.
12 X 12	305 X 305	1	6.0	2.7
18 X 18	457 X 457	2	11.1	5.0
24 X 24	610 X 610	2	17.4	7.9
24 X 36	610 X 914	4	24.3	11.0

Wall or ceiling opening is W + 3/8" (9 mm)

For detailed specifications see submittal sheet

