

# FA-300 Retrofit

## FLOOR DOOR / 300 lb./sq. ft loading

### Application

- Designed for interior and exterior applications where watertightness is not required.
- For use when the door will not be cast into concrete, but bolted down.

### Product Features FA-300-R

- Angle frame construction designed to be bolted into an existing opening
- Diamond plate door panel is equipped with a flush aluminum drop handle and an automatic hold open arm

### FA-300 Retrofit Floor Door Specifications:

**Material:** Aluminum door and frame; stainless steel hinges and hardware

**Door:** 1/4" aluminum diamond plate reinforced for live load of 300 pounds/sq ft.

**Frame:** Angle frame fabricated from aluminum extrusion

**Hinge:** Stainless steel butt hinges with tamperproof stainless steel bolts and nuts

**Opening Device:** Automatic hold open arm with red vinyl grip allows door panel to open to 90 degrees, locking door in open position, and allowing for easy control when closing door panel.

When required, stainless steel compression springs can be provided to add lift assistance.

*Available with electrical actuators, operated by wall mounted push button switch, and remote control*

**Standard Latch:** Flush aluminum drop handle with staple for padlock. Also available recessed padlock provision: st/stl slamlock

**Finish:** Mill finish, with optional bituminous coating on exterior of frame



### FA-300-RETROFIT STANDARD SIZES

(Other sizes available upon request)

| Nominal Door Size W&H |             | Weight per Door |       |
|-----------------------|-------------|-----------------|-------|
| Inches                | (mm)        | lbs.            | (kg.) |
| 24 x 24               | 610 x 610   | 42              | 19    |
| 24 x 30               | 610 x 762   | 49              | 22    |
| 24 x 36               | 610 x 914   | 55              | 25    |
| 30 x 30               | 762 x 762   | 57              | 26    |
| 30 x 48               | 762 x 1219  | 80              | 36    |
| 36 x 36               | 914 x 914   | 73              | 33    |
| 36 x 48               | 914 x 1219  | 92              | 42    |
| 42 x 42               | 1067 x 1067 | 94              | 43    |
| *48 x 48              | 1219 x 1219 | 123             | 56    |
| *48 x 72              | 1219 x 1829 | 170             | 77    |
| *60 x 60              | 1524 x 1524 | 177             | 80    |

\*Double Leaf

For detailed specifications see submittal sheet

