

GFRG-R

GLASS FIBER REINFORCED GYPSUM RADIUS CORNER

Application

Glass fiber reinforced gypsum, ceiling access doors are designed to blend seamlessly into drywall ceilings.

Product Features

- Tapered edge for joint tape
- Easily textured
- Lightweight
- No cracking or shrinkage
- Mold and moisture resistant

GFRG-R Access Door Specifications:

- Shell Thickness = 1/8" to 3/16"
- Fastener Test Pull Out (wood stud) = 525 lb. avg.
- Fastener Test Pull Out (metal stud) = 215 lb. avg.
- Fastener Push Through Test = 350 lb. avg.
- Fuel Contribution (ASTM-E84-80) = 0
- Flame Spread (ASTM-E84-80) = 0
- Smoke Index (ASTM-E84-80) = 0
- Combustion (ASTM-E84-80) = 0
- CLASS A NON-RATED

GFRG-R STANDARD SIZES

(Special sizes available upon request)

Door Size	Ceiling Opening	Weight
Inches (mm)	Inches (mm)	LBS (kg)
9 x 9 (229 x 229)	15 x 15 (381 x 381)	5.6 (2.5)
12 x 12 (305 x 305)	18 x 18 (457 x 457)	8.2 (3.7)
16 x 16 (406 x 406)	22 x 22 (559 x 559)	11.3 (5.1)
18 x 18 (457 x 457)	24 x 24 (610 x 610)	14.7 (6.7)
24 x 24 (610 x 610)	30 x 30 (762 x 762)	16.9 (7.7)

For detailed specifications see submittal sheet

