

ALUMINUM LADDER ACCESS ROOF HATCH

Application

Acudor Ladder Access Roof Hatches are designed to provide convenient, economical access to the roof of a building

Features RHA

- Weather tight construction
- 12" high insulated curb
- Stainless Steel Hardware

Optional Features RHA

- Painted and Anodized finishes
 Polycarbonate domes for daylighting
 - Curb Mounted Units

Convenient one-hand operation

• Supports 40lbs./sq. ft. live load

- Louvered Curbs
- Curb pitch corrected for sloped roof
- Higher curb heights for "green roof" applications

RHA Specifications:

- Cover: Double-skin construction ("in box type design") with 1" Polyiso (R-6) insulation and a continuous EPDM foam weather/draft seal gasket that is attached to the inside of cover to provide a flush, tight fit. Designed to support a live load of 40lbs./sq. ft., the cover is 11 gauge aluminum with a 20 gauge aluminum inside liner.
- Curb: 11 gauge aluminum with 1" thick Polyiso (R-6) insulation at curb exterior. Curb is 12" high, with 3.375" wide bottom flange an pre-drilled mounting holes.

Hinge: Heavy duty Aluminum pintle hinges with 3/8" SS pin

Opening: Gas spring operators allow cover to open and close with ease. Stainless Steel Inside pull handle allows for easy control when closing cover.

Door Latch: Self latching, Stainless steel outside T handle with stainless steel inside lock and lever assembly. Unit also has inside and outside padlock provisions.

Finish: Mill finish.

RHA STANDARD SIZES (other sizes available)

	Curb ID W&L	Weight per Hatch
Model	inches (mm)	lbs. (kg.)
A3232	24 x 24 (610 x 610)	60 (27.3)
A3238	24 x 30 (610 x 762)	65 (29.4)
A3244	24 X 36 (610 X 914)	70 (31.8)
A3838	30 x 30 (762 x 762)	80 (36.2)
A3844	30 x 36 (762 x 914)	85 (38.6)
A4444	36 x 36 (914 x 914)	95 (43.2)

For detailed specifications see submittal sheet





U.S.A.: info@acudor.com / 800.722.0501 MEXICO: infomx@acudor.com / +52 844 171 6595

CANADA: info@acudor.ca / 844.228.3671 **INDIA / MIDDLE EAST / NORTH AFRICA:** ap-imea@acudor.com / +971-4-399-6966

INTERNATIONAL: info@acudorintl.com / 905.428.2240 SITE: www.acudor.com

This document contains proprietary information which is the property of Acudor Products. It shall not be modified, copied, furnished, nor distributed (in whole or in part) without proper authorization. Copyright © 2020 Acudor Products.