

# MS-7000

## SECURITY DOORS for Medium Security

### Application

- For use in medium security jails, prisons, psychiatric institutions, etc.
- Medium duty security access door

### Product Features

- 12 Gauge door and frame
- A one piece trim flange and continuous concealed hinge
- Door panel features rounded safety corners

### MS-7000 Access Door Specifications:

**Material:** Steel or Stainless Steel

**Door / Mounting Frame:** 12 gauge door and mounting frame

Flush to frame with rounded corners and reinforced panel

One piece outer flange welded to mounting frame

**Hinge:** Continuous, concealed

**Standard Latch:** Tamper resistant allen head cam latch  
with security pin

**Optional Latches/Locks:** Spanner head cam latch,  
cylinder lock & key. When master keying is required, doors  
can be prepared for rim or mortise cylinder locks

**Finish:** Baked White Prime Coat

(Additional finish paint is recommended for superior  
corrosion resistance)

### MS-7000 STANDARD SIZES

(other sizes available upon request)

Nominal Door Size W&H		Weight per Door	
inches	mm	lbs.	kg.
12 x 12	305 x 305	10	4.5
16 x 16	406 x 406	15	7.0
18 x 18	457 x 457	18	8.3
24 x 24	610 x 610	29	13.2
24 x 36	610 x 914	40	18.3
36 x 36	914 x 914	61	27.4

Wall or ceiling opening is W + 3/8" (9 mm)

For detailed specifications see submittal sheet

