

SF-2000

Surface Mounted Access Door

Application

- An innovative surface mounted access door for all types of walls and ceilings

Product Features

- An exposed continuous piano hinge allows the door panel to open to 175 degrees
- There is no frame to extend into the wall or ceiling
- Perfect for access to odd size openings

SF-2000 Access Door Specifications:

Door / Door Frame: Steel: 16 gauge, flush to frame with rounded safety corners and a one piece outer flange
Frame is one piece outer flange

Hinge: Exposed continuous piano hinge

Standard Latch: Stainless Steel Slotted Screwdriver Cam Latch

Optional Latches/Locks: Cylinder lock & key, allen head cam latch, spanner head cam latch

Finish: Baked White Prime Coat

(Additional finish paint is recommended for superior corrosion resistance)



SF-2000 STANDARD SIZES

(other sizes available upon request)

Nominal Door Size W&H		Latches	Weight per Door	
Inches	mm		lbs.	kg.
8 X 8	203 X 203	1	2.0	0.9
12 X 12	305 X 305	1	3.9	1.8
16 X 16	406 X 406	2	6.3	2.9
24 X 24	610 X 610	4	12.7	5.8

Wall opening is normal door size minus - 1/4" (6 mm)

For detailed specifications see submittal sheet

